



# PRODUCT SPEC SHEET

**SKU 203486**

**Model:VT-8-20**

**EAN:3800170241053**

## VT-8-20 20W LED GRILL FITTING 566MM CREE CHIP 4000K 6YRS WTY 120LM/W



**IP20**  
STANDARD



- Prismatic Fitting designed with Lumen efficiency 120LM/W
- Fitted with high efficiency SMD-CREE Chip that offer up to 85% in energy savings
- Quick Connector for easy installation
- 50% less power consumption compared to traditional grill fitting lighting
- Switch cycles: >15000
- Instant start-up in less than 1 second
- Applications - Residential, Hotels, Malls, Office and many more

## TECHNICAL INFORMATION

|                               |                   |
|-------------------------------|-------------------|
| <b>Dimmable:</b>              | No                |
| <b>On/Off Cycles:</b>         | >15000            |
| <b>Instant Start:</b>         | 0-100% in <1s     |
| <b>Model:</b>                 | VT-8-20           |
| <b>Color Temperature:</b>     | 4000K             |
| <b>CRI:</b>                   | >80               |
| <b>Watts:</b>                 | 20                |
| <b>Lumens:</b>                | 2400              |
| <b>Input Power:</b>           | AC:220-240V, 50Hz |
| <b>Unit Color:</b>            | White             |
| <b>Color for Web:</b>         | Day White         |
| <b>Body Type:</b>             | Plastic           |
| <b>Dimension:</b>             | 566x76x24mm       |
| <b>Operation Temperature:</b> | -20°C to +40°C    |

## LISTING DETAILS

|                        |               |
|------------------------|---------------|
| <b>SKU:</b>            | 203486        |
| <b>Model:</b>          | VT-8-20       |
| <b>EAN:</b>            | 3800170241053 |
| <b>Commodity Code:</b> | 9405110000    |

## PACKAGING

|                            |             |
|----------------------------|-------------|
| <b>Gross Weight (Kgs):</b> | 0.24        |
| <b>Unit CBM:</b>           | 0.001783    |
| <b>Dimension:</b>          | 566x76x24mm |

## MASTER BOX PACKAGING

|                         |    |
|-------------------------|----|
| <b>Box Qty:</b>         | 30 |
| <b>Qty Per Pallet:</b>  |    |
| <b>Length (Box) mm:</b> | 80 |

|                      |               |
|----------------------|---------------|
| PF:                  | >0.7          |
| LED Chip Type:       | SMD-CREE Chip |
| Beam Angle:          | 120°          |
| Energy Rating Label: | E (2021)      |
| Energy Saving:       | 85 Energy     |
| IP Rating:           | IP20          |
| IK Rating:           | IK06          |
| Long Life:           | 30,000 Hours  |
| lumens per watt:     | 120           |

|                  |     |
|------------------|-----|
| Width (Box) mm:  | 30  |
| Height (Box) mm: | 605 |