



PRODUCT SPEC SHEET

SKU 218776

Model:VT-291

EAN:3800170240704

VT-291 7.5W GU10 PLASTIC SPOTLIGHT CREE CHIP 6500K 38'D 6YRS WTY



IP20
STANDARD



- Stable SMD-CREE Chip technology for better reliability
- Lasts 25,000 Hours, longer life span than Standard halogen spotlights
- Replaces 70 watts old halogen lamp
- Easy to install, designed with GU10 base
- Applications - Hotels, Bars, Commercial and Residential Lighting and Exhibition Stands etc

TECHNICAL INFORMATION

Dimmable:	No
On/Off Cycles:	>20000
Model:	VT-291
Color Temperature:	6500K
CRI:	>80
Watts:	7.5
Lumens:	610
Input Power:	AC:220-240V, 50Hz
Equivalence Watts:	70
Unit Color:	White
Color for Web:	White
Body Type:	Plastic
Dimension:	50x55mm
Operation Temperature:	-20°C to +45°C

LISTING DETAILS

SKU:	218776
Model:	VT-291
EAN:	3800170240704
Commodity Code:	8539521000

PACKAGING

Gross Weight (Kgs):	0.03
Unit CBM:	0.000234
Dimension:	50x55mm

MASTER BOX PACKAGING

Box Qty:	200
Qty Per Pallet:	
Length (Box) mm:	50
Width (Box) mm:	50

Base:	GU10
LED Chip Type:	SMD-CREE Chip
Beam Angle:	38°
Energy Rating Label:	F (2021)
Energy Saving:	80 Energy
IP Rating:	IP20
Long Life:	25,000 Hours

Height (Box) mm:80