



PRODUCT SPEC SHEET

SKU 218806

Model:VT-271

EAN:3800170240643

VT-271 10W GU10 LED PLASTIC SPOTLIGHT MILKY COVER CREE CHIP 6500K 100'D 6YRS WTY



IP20
STANDARD



- New Range of GU10 Spotlights with SMD-CREE Chip technology for better reliability
- Lasts 25,000 Hours, longer life span than Standard halogen spotlights
- Replaces 70 watts old halogen lamp
- Easy to install, designed with GU10 base
- Applications - Hotels, Bars, Commercial and Residential Lighting and Exhibition Stands etc

TECHNICAL INFORMATION

Dimmable:	No
On/Off Cycles:	>20000
Model:	VT-271
Color Temperature:	6500K
CRI:	>80
Watts:	10
Lumens:	1000
Input Power:	AC:220-240V, 50Hz
Equivalence Watts:	70
Unit Color:	White
Color for Web:	White
Body Type:	Plastic
Dimension:	50x56.5mm

LISTING DETAILS

SKU:	218806
Model:	VT-271
EAN:	3800170240643
Commodity Code:	8539521000

PACKAGING

Gross Weight (Kgs):	0.03
Unit CBM:	0.00023
Dimension:	50x56.5mm

MASTER BOX PACKAGING

Box Qty:	200
Qty Per Pallet:	
Length (Box) mm:	50

Operation Temperature:	-20°C to +45°C
Base:	GU10
LED Chip Type:	SMD-CREE Chip
Beam Angle:	100°
Energy Rating Label:	F (2021)
Energy Saving:	80 Energy
IP Rating:	IP20
Long Life:	25,000 Hours

Width (Box) mm:	50
Height (Box) mm:	80