



PRODUCT SPEC SHEET

SKU 240026

Model:VT-80068-W

EAN:3800170240865

VT-80068 8W LED BEDSIDE WALL LIGHT WITH USB/PD CHARGING CREE CHIP 3000K WHITE BODY



IP20
STANDARD

02
YEAR
WARRANTY



- New Range of Bedside wall light with SMD-CREE Chip technology for better reliability
- USB/PD Fast Charging(Max 20W)
- 350° rotatable and 90° horizontally adjustable
- Strong and sturdy Aluminium+PC body
- USB Output DC:5V,3A/9V,2A/12V,1.5A and PD Output DC:5V,3A/9V,2.25A/12V,1.5A
- 2IN1 spotlight for reading and wall light for back glow
- With 2 independent switches to control backlight and spotlight
- Applications - Suitable for Bed Rooms, showrooms & Boutiques etc

TECHNICAL INFORMATION

USB Output:	DC:5V, 3A/9V, 2A/12V, 1.5A
On/Off Cycles:	>15000
Model:	VT-80068-W
Color Temperature:	3000K
CRI:	>80
Watts:	8
Lumens:	830
Input Power:	AC:220-240V, 50Hz
Unit Color:	White
Color for Web:	Warm White
Body Type:	Aluminium+PC
Dimension:	132x80x132mm

LISTING DETAILS

SKU:	240026
Model:	VT-80068-W
EAN:	3800170240865
Commodity Code:	9405110000

PACKAGING

Gross Weight (Kgs):	0.4
Unit CBM:	0.001892
Dimension:	132x80x132mm

MASTER BOX PACKAGING

Box Qty:	20
-----------------	----

LED Chip Type:	SMD-CREE Chip
Beam Angle:	40°
Energy Rating Label:	F (2021)
IP Rating:	IP20
Long Life:	20,000 Hours

Qty Per Pallet:	
Length (Box) mm:	135
Width (Box) mm:	85
Height (Box) mm:	140