



PRODUCT SPEC SHEET

SKU 232166

Model:VT-4455

EAN:3800170252295

VT-4455 50W FLOODLIGHT CREE CHIP 4000K BLACK BODY GREY GLASS 135LM/W 6YRS WTY IP65



IP65
STANDARD



- New Range of LED Floodlights powered with high quality SMD-CREE Chip
- Product designed with high lumen efficiency of 135 LM/W
- Built Strong and durable with Aluminium - Corrosion resistant design
- IP65 rated outdoor protection with a warranty period of 6 Years
- Suitable for building facades, sports facilities, industrial, commercial billboards, hoardings, parking lots etc.

TECHNICAL INFORMATION

Dimmable:	No
Instant Start:	0-100% in <1s
Model:	VT-4455
Color Temperature:	4000K
CRI:	>70
Watts:	50
Lumens:	6750
Useful Lumens:	5740
Input Power:	AC:220-240V, 50Hz
Unit Color:	Black
Color for Web:	Day White
Body Type:	Aluminium
Dimension:	185x35x162mm
Operation Temperature:	-20°C to +45°C

LISTING DETAILS

SKU:	232166
Model:	VT-4455
EAN:	3800170252295
Commodity Code:	9405429000

PACKAGING

Gross Weight (Kgs):	0.59
Unit CBM:	0.001715
Dimension:	185x35x162mm

MASTER BOX PACKAGING

Box Qty:	10
Qty Per Pallet:	
Length (Box) mm:	190

LED Chip Type:	SMD-CREE Chip
Beam Angle:	115°
Energy Rating Label:	D (2021)
Energy Saving:	85 Energy
IP Rating:	IP65
Long Life:	30,000 Hours
lumens per watt:	135

Width (Box) mm:	39
Height (Box) mm:	174