



PRODUCT SPEC SHEET

SKU 232216

Model:VT-44201

EAN:3800170252356

VT-44201 200W FLOODLIGHT CREE CHIP 1M WIRE 6500K BLACK BODY 135LM/W 6YRS WTY IP65



IP65
STANDARD



- New Range of LED Floodlights powered with high quality SMD-CREE Chip
- Product designed with high lumen efficiency of 135 LM/W
- Built Strong and durable with Aluminium - Corrosion resistant design
- Comes with 1m wire length
- IP65 rated outdoor protection with a warranty period of 6 Years
- Suitable for building facades, sports facilities, industrial, commercial billboards, hoardings, parking lots etc.

TECHNICAL INFORMATION

Dimmable:	No
Instant Start:	0-100% in <1s
Model:	VT-44201
Color Temperature:	6500K
CRI:	>70
Watts:	200
Lumens:	27000
Useful Lumens:	22960
Input Power:	AC:220-240V, 50Hz
Unit Color:	Black
Color for Web:	White
Body Type:	Aluminium
Dimension:	406x47x333mm

LISTING DETAILS

SKU:	232216
Model:	VT-44201
EAN:	3800170252356
Commodity Code:	9405429000

PACKAGING

Gross Weight (Kgs):	2.95
Unit CBM:	0.00981
Dimension:	406x47x333mm

MASTER BOX PACKAGING

Box Qty:	2
Qty Per Pallet:	

Operation Temperature:	-20°C to +45°C
LED Chip Type:	SMD-CREE Chip
Beam Angle:	115°
Energy Rating Label:	D (2021)
Wire Length:	1m
Energy Saving:	85 Energy
IP Rating:	IP65
Long Life:	30,000 Hours
lumens per watt:	135

Length (Box) mm:	411
Width (Box) mm:	52
Height (Box) mm:	345