



PRODUCT SPEC SHEET

SKU 238256

Model:VT-44003

EAN:3800170252363

VT-44003 300W LED FLOODLIGHT CREE CHIP 1M WIRE 4000K BLACK BODY 135LM/W 6YRS WTY IP65



IP65
STANDARD



- New Range of LED Floodlights powered with high quality SMD-CREE Chip
- Product designed with high lumen efficiency of 135 LM/W
- Built Strong and durable with Aluminium - Corrosion resistant design
- Comes with 1m wire length
- IP65 rated outdoor protection with a warranty period of 6 Years
- Suitable for building facades, sports facilities, industrial, commercial billboards, hoardings, parking lots etc.

TECHNICAL INFORMATION

Dimmable:	No
Instant Start:	0-100% in <1s
Model:	VT-44003
Color Temperature:	4000K
CRI:	>70
Watts:	300
Lumens:	40500
Useful Lumens:	34440
Input Power:	AC:220-240V, 50Hz
Unit Color:	Black
Color for Web:	Day White
Body Type:	Aluminium
Dimension:	498x48x411.6mm

LISTING DETAILS

SKU:	238256
Model:	VT-44003
EAN:	3800170252363
Commodity Code:	9405429000

PACKAGING

Gross Weight (Kgs):	4.96
Unit CBM:	0.015017
Dimension:	498x48x411.6mm

MASTER BOX PACKAGING

Box Qty:	2
Qty Per Pallet:	

Operation Temperature:	-20°C to +45°C
LED Chip Type:	SMD-CREE Chip
Beam Angle:	115°
Energy Rating Label:	D (2021)
Wire Length:	1m
Energy Saving:	85 Energy
IP Rating:	IP65
Long Life:	30,000 Hours
lumens per watt:	135

Length (Box) mm:	505
Width (Box) mm:	55
Height (Box) mm:	420