



PRODUCT SPEC SHEET

SKU 216576

Model:VT-151

EAN:3800170253223

VT-151 20W T8 NANO PLASTIC TUBE NON ROTATABLE 150CM CREE CHIP 4000K 6YRS WTY



IP20
STANDARD



- New Range of LED Tubes powered with high quality SMD-CREE Chip
- Nano-plastic tube offers better light transmittance
- Higher endurance and longevity compared to PC and glass
- Cost effective, safe retrofit for T8 Tubes
- Super thermal conductivity - Constant current integrated IC driver
- Wide light angle effectively diffuses glare
- Suitable for domestic and commercial lighting, offices, supermarkets, shops, hotels and many more

TECHNICAL INFORMATION

Dimmable:	No
On/Off Cycles:	>15000
Model:	VT-151
Color Temperature:	4000K
CRI:	>80
Watts:	20
Lumens:	2100
Input Power:	AC:220-240V, 50Hz
Unit Color:	White
Color for Web:	Day White
Body Type:	Plastic
Dimension:	1500x28mm
Base:	G13

LISTING DETAILS

SKU:	216576
Model:	VT-151
EAN:	3800170253223
Commodity Code:	8539522000

PACKAGING

Gross Weight (Kgs):	0.21
Unit CBM:	0.00168
Dimension:	1500x28mm

MASTER BOX PACKAGING

Box Qty:	25
Qty Per Pallet:	

Shape:	T8
PF:	>0.7
LED Chip Type:	SMD-CREE Chip
Beam Angle:	160°
Energy Rating Label:	F (2021)
Energy Saving:	80 Energy
IP Rating:	IP20
Long Life:	25,000 Hours
lumens per watt:	100

Length (Box) mm:	29
Width (Box) mm:	29
Height (Box) mm:	1558