



PRODUCT SPEC SHEET

SKU 239996

Model:VT-88061-B

EAN:3800170240834

VT-88061 2W LED BEDSIDE LIGHT ALUMINUM+PC CREE CHIP 3000K BLACK BODY IP20



IP20
STANDARD

02
YEAR
WARRANTY

CREE
LED
POWERED

- New Range of Bedside wall light with SMD-CREE Chip technology for better reliability
- Perfect choice of Interior lighting for fabulous aesthetics and appeal
- Efficient LED driver and intruded heat sink for longer lifespan
- Recessed installation with a cutting size of 142.57mm
- Elegant Black color finish
- Applications - Suitable for Bed Rooms, showrooms & Boutiques etc

TECHNICAL INFORMATION

On/Off Cycles:	>15000
Cutting Size:	142.57mm
Model:	VT-88061-B
Color Temperature:	3000K
CRI:	>80
Watts:	2
Lumens:	76
Input Power:	AC:220-240V, 50Hz
Unit Color:	Black
Color for Web:	Warm White
Body Type:	Aluminium+PC
Dimension:	65x59x150mm
LED Chip Type:	SMD-CREE Chip

LISTING DETAILS

SKU:	239996
Model:	VT-88061-B
EAN:	3800170240834
Commodity Code:	9405110000

PACKAGING

Gross Weight (Kgs):	0.23
Unit CBM:	0.000853
Dimension:	65x59x150mm

MASTER BOX PACKAGING

Box Qty:	50
Qty Per Pallet:	

Beam Angle:	25°
Energy Rating Label:	G (2021)
IP Rating:	IP20
Long Life:	20,000 Hours

Length (Box) mm:	70
Width (Box) mm:	65
Height (Box) mm:	155