



PRODUCT SPEC SHEET

SKU 240006

Model:VT-80062-W

EAN:3800170240841

VT-88062 2W LED BEDSIDE LIGHT ALUMINUM+PC CREE CHIP 3000K WHITE BODY IP20



IP20
STANDARD

02
YEAR
WARRANTY

CREE
LED
POWERED

- New Range of Bedside wall light with SMD-CREE Chip technology for better reliability
- Perfect choice of Interior lighting for fabulous aesthetics and appeal
- USB/PD Fast Charging(Max 20W)
- USB Output DC:5V,3A/9V,2A/12V,1.5A and PD Output DC:5V,3A/9V,2.25A/12V,1.5A
- Elegant White color finish
- Applications - Suitable for Bed Rooms, showrooms & Boutiques etc

TECHNICAL INFORMATION

USB Output:	DC:5V, 3A/9V, 2A/12V, 1.5A
On/Off Cycles:	>15000
Model:	VT-80062-W
Color Temperature:	3000K
CRI:	>80
Watts:	2
Lumens:	60
Input Power:	AC:220-240V, 50Hz
Unit Color:	White
Color for Web:	Warm White
Body Type:	Aluminium+PC
Dimension:	250x115x140mm
LED Chip Type:	SMD-CREE Chip

LISTING DETAILS

SKU:	240006
Model:	VT-80062-W
EAN:	3800170240841
Commodity Code:	9405110000

PACKAGING

Gross Weight (Kgs):	0.58
Unit CBM:	0.005662
Dimension:	250x115x140mm

MASTER BOX PACKAGING

Box Qty:	20
Qty Per Pallet:	

Beam Angle:	162°
Energy Rating Label:	G (2021)
IP Rating:	IP20
Long Life:	20,000 Hours

Length (Box) mm:	165
Width (Box) mm:	125
Height (Box) mm:	245