



PRODUCT SPEC SHEET

SKU 2162856

Model:VT-1249

EAN:3800170240971

VT-1249 36W LED WP G-SERIES TUBE 120CM CREE CHIP 4000K 6YRS WTY 130LM/W



IP65
STANDARD

6
YEAR
WARRANTY

CREE
LED
POWERED

Super Bright
130
LUMENS/W

- Designed with high efficiency SMD-CREE Chip technology which makes it more reliable and durable
- Powerful LED light source with high lumen efficiency of 130 LM/W
- Linkable Upto 8 Units
- Complete protection from water, dust and corrosion - IP65 Rated
- Designed for maximum efficiency & minimal glare
- Excellent heat dissipation
- Suitable for parking lots, warehouses, garages, storage docks, workshops etc.

TECHNICAL INFORMATION

Dimmable:	No
On/Off Cycles:	>25000
Instant Start:	0-100% in <1s
Model:	VT-1249
Color Temperature:	4000K
CRI:	>80
Watts:	36
Lumens:	4820
Input Power:	AC:220-240V, 50/60Hz
Unit Color:	White
Color for Web:	Day White
Body Type:	PC
Dimension:	1200x66x58mm
PF:	>0.9

LISTING DETAILS

SKU:	2162856
Model:	VT-1249
EAN:	3800170240971
Commodity Code:	94051140

PACKAGING

Gross Weight (Kgs):	0.91
Unit CBM:	0.007303
Dimension:	1200x66x58mm

MASTER BOX PACKAGING

Box Qty:	12
Qty Per Pallet:	
Length (Box) mm:	

LED Chip Type:	SMD-CREE Chip
Beam Angle:	120°
Energy Rating Label:	E (2021)
Linkable:	Upto 8 Units
IP Rating:	IP65
IK Rating:	IK05
Long Life:	50,000 Hours
lumens per watt:	130

Width (Box) mm:
Height (Box) mm: