

Data Sheet						
Brand:	Motorola					
Product Name:	Motorola 125W TurboPower Wall Charger					
Product SKU:	SJMCD1252					
Model#:	MCD-1252					
Description:	Motorola 125W Dual Port TurboPower Wall Charger					
USP1:	UNBELIEVABLY FAST AND COMPACT - The latest in GaNFast™ technology enables astonishingly fast 125W TurboPower charging in an incredibly compact and portable form factor.					
USP2:	REMARKABLY POWERFUL - Using Gallium Nitride (GaN) technology it is able to pack a massive amount of power into a compact form factor thanks to high energy efficiencies compared to legacy silicone.					
USP3:	TRAVEL FRIENDLY - Smaller than most laptop chargers it becomes a great all in one travel charger option for USB-C phones, tablets, and high-powered laptops.					
USP4:	CHARGE SAFETLY. REST EASY - Safty compliances approved. Get built-in protection from power surges, extreme heat, and other dangers, and know your smartphone or tablet will remain safe while charging.					
USP5:	HIGH EFFICIENCY CHARGING AND ENVIRONMENTAL FRIENDLY - The TurboPower 125W boasts Level VI High Energy Efficiency. It is also halogen-free and PVC-free.					
USP6:	TURBOPOWER SHARE - Capable of Intelligent power sharing between two ports for charging 2 devices at the same time.					
USP7:	Special 6.5 Amp Cable- Comes with e-marked high current cable that enables safe and fast power transfer between compatible chargers and usbc devices.					
Charger Information:						
Color:	Black		Output Port:	USB-C (Type-C)		
Dimensions (mm):	101.4 X 56 x 29		Weight (g):	161.5±5		
Charger Electrical Specifications:						
Charging Protocols:	GaN Fast Charging Technology					
Input:	100-240V ~50/60 Hz 2.0A					
Output:	Single Port Output (USB-C1/USB-C2)	5.0V~3.0A	15.0W			
		9.0V~3.0A	27.0W			
		15.0V~3.0A	45.0W			
		20.0V~6.25A	125W Max or			
		5.0C-20.0V~6.25A	125.0W Max			
	Duo Port Output (USBC-1 + USB-C2)	120W Max				
Operating Temperature:	-10°C ~ +45°C (14~113°F) @ 90% relative humidity (non-condensing)					
Storage Temperature:	-40°C ~ +85°C (-40~185°F)					
Ambient Temperature	25°C ± 3°C (77°F±5.4°F)					
Charger Compliance Certification:						
CE	Yes (LVD and EMC)		Kvalitet (Serbia)	Yes		
Ukr (Ukraine)	Yes					
Charging Cable						
Cable	Motorola USB-C to USB-C 6.5A cable or compatible cable		Model# (1m):	MC062CCB10A		
Charging Cable Requirement:						
Retail Box (SJMCD1252)	Type of packaging:	Retail box				
	Width (mm):	90		Master Carton Pack QTY:	20	
	Height (mm):	155		Master Carton Width (m):	0.38	
	Depth (mm):	32		Master Carton Depth (m):	0.192	
	Weight (g):	242±5		Master Carton Height (m):	0.188	
	EAN	6955226416750		Master Carton Gross Weight (Kg):	5.84±1	