



EARBUDS 3C-S

Product Specifications

Model	Earbuds 3C-S	
		
Styling	In-ear	
Color version	BLACK / WHITE Total 2 colors	
Connectivity	Wired	
Speaker Driver		
Driver size (mm)	9.4 mm	
Frequency response	20-20 KHz	
Sensitivity dB @ 1KHz +/- 3dB	96±3dB/ F=1KHz,p=1mW(0.178V R.M.S)	
Impedance	32Ω±15%	
Max power	5 mW	
Mic for call		
Microphones	1 x mic	
Sensitivity dB @ 1KHz +/- 3dB	-42 dB	
UIS (control)		
Buttons	1 x tact switch	
Jacks / plugs		
Analog Audio in	Yes	
Accessories		

Cables (length)	Built-in cable with Type C pin (L= 1.2 m)
Packaging	
Retail box	Paper closed box
No. in pack / outer	
Total Weight (including packaging)	
Carton box (Packaging) Dimensions (LxWxH)	
Gift box	Paper box with window
Gift box Dimensions (LxWxH)	
Headphones Dimensions (LxWxH)	
Headphones weight	
Packaging Weight (gross) (including USB charging case,QSG,silicon caps & warranty sheet)	
Operation temperature	0°C ~+45°C
Storage temperature	-20°C ~+70°C