

MMR-88


AM / FM / Multi-Powered Radio



Color



Yellow



AUTO SCAN



STEREO BY EARPHONE



USB PORT



FLASHLIGHT



DYNAMO

Main Features

- AM / FM
- 19 Random Preset Stations (AM / FM Mixed)
- Powered by Hand Crank / Solar Panel / DC-In (USB Type-C) to Rechargeable Lithium Battery
- Charging LED Indicator
- Adjustable LED Flashlight (Hi / Low / Blinking / SOS Morse Code)
- Built-In Clock
- Built-In Speaker
- Stereo Earphone Port
- Emergency Buzzer
- 90-Minute Auto Shut-Off
- Stereo Earphone Port
- Hand-Held Size
- DC-Out (5V/0.3A) USB Type-A for Charging Smaller Devices
- DC-In (5V/0.5A) USB Type-C for Recharging
- USB Type-A to USB Type-C Cable and Hand Strap Included

- EAN-code: 47.11317.99865.7 (YELLOW)

Dimensions:

Dim. Unit : 52 x 69.8 x 83.6 mm (WxDxH)

Net / Gross weight of single device : 0.38 / 0.6 (kg)

Net / Gross weight of packaging : 6.3 / 6.9 (kg)

Container quantity :

20' ft : 9680 (pcs)

40' ft : 19360 (pcs)

