



MMR-88 DAB

DAB+ / FM-RDS / Multi-Powered Radio



Color

Yellow



Main Features

- Digital DAB+/FM
- 40 Station Presets (20 DAB+/20 FM)
- Powered by Hand Crank / Solar Panel / DC-In (USB Type-C) to Rechargeable Lithium Battery
- Charging LED Indicator
- Adjustable LED Flashlight (Hi / Low / Blinking / SOS Morse Code)
- Built-In Clock
- Built-In Speaker
- Stereo Earphone Port
- Hand-Held Size
- DC-Out (5V/0.3A) USB Type-A for Charging Smaller Devices
- DC-In (5V/0.5A) USB Type-C for Recharging
- USB Type-A to USB Type-C Cable and Hand Strap Included

The MMR-88DAB is a rechargeable emergency radio ready for anything. It can be charged from hand cranking, DC-In power by USB Type-C or even the solar panel! The radio itself not only works as a portable battery to charge other smaller devices, it is also a flashlight with different lighting patterns for all situations.

• EAN-code: 47.11317.99866.4 (YELLOW)

Dimensions:

Dim. Unit : 152 x 69.8 x 83.6 mm (WxDxH)

Net / Gross weight of single device : 0.38 / 0.58 (kg)

Net / Gross weight of packaging : 6.1 / 6.7 (kg)

Container quantity :

20' ft : 9680 (pcs)

40' ft : 19360 (pcs)

