

Ecovacs Deebot T30C Gen 2 0,26 l Beutellos Schwarz

Marke : Ecovacs

Artikel-Code: DLX71

Produktname : Deebot T30C Gen 2

Ecovacs Deebot T30C Gen 2. Staubbehälter Typ: Beutellos, Produktfarbe: Schwarz, Form: Rund.
Staubkapazität (gesamt): 0,26 l, Geräuschpegel: 65 dB, Staubkapazität (Basis): 3 l. Akku-
/Batterietechnologie: Lithium-Ion (Li-Ion), Laufzeit: 180 min, Akku-/Batteriespannung: 12 V. Höhe: 100
mm, Breite: 353 mm, Tiefe: 352 mm



Design		Leistungen	
Staubbehälter Typ *	Beutellos	Unterstützte mobile Betriebssysteme	Android, iOS
Produktfarbe *	Schwarz	Funktioniert mit Google Assistant	✓
Form	Rund	Funktioniert mit Amazon Alexa	✓
Fernbedienung	✓	Funktionen der Apps	Virtuelle Wand
Smartphone Fernsteuerung	✓	Energie	
Stoßstangenschutz	✓	Akku-/Batterietechnologie *	Lithium-Ion (Li-Ion)
Leistungen		Akku-/Batteriespannung	12 V
Nasswischen *	✓	Laufzeit *	180 min
Staubkapazität (gesamt) *	0,26 l	Ladezeit	1 h
Staubkapazität (Basis)	3 l	Gewicht und Abmessungen	
Kapazität des schmutzwasserbehälters (Basis)	4 l	Höhe	100 mm
HEPA Filtrationsystem *	✓	Breite	353 mm
HEPA-Klasse	HEPA 10	Tiefe	352 mm
Automatische Rückkehr zur Basisstation *	✓	Basisstation Abmessungen (B x T x H)	353 x 477 x 533 mm
Funktionen der Basisstation	Ladend, Purification	Gesamtgewicht	11,3 kg
Hindernisüberwindung bis zu	2 cm	Lieferumfang	
Bürstentyp	Walzenbürste & Seitenbürste	Betriebsanleitung	✓
unterstützte Bodenflächen	Harter Boden, Laminat, Parkett, Vinyl, Holz	Basisstation	✓
Integrierte Sensoren	Laser	Netzkabel enthalten	✓
Navigationstyp	Laser Distance Sensor (LDS), TruEdge 3D	Technische Details	
Geräuschpegel *	65 dB	Saugleistung	25000 Pascal



6970135036370



6970135037513

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.