

Samsung Galaxy Tab A11+ 5G (11")

Marke : Samsung

Artikel-Code: SM-X236BZSREUB



Produktname : Galaxy Tab A11+ 5G (11")

- Eintauchen & Genießen: Flüssige Bilder dank 90 Hz Bildwiederholrate, satter Sound über Quad-Lautsprecher & 25W-Schnellladen¹ für Entertainment ohne Kompromisse
- Erlebe AI: Smarte Funktionen direkt auf deinem Tablet mit Google Gemini² & Circle to Search mit Google³
- Smart notiert: Notizen einfach erstellen & organisieren mit Samsung Notes
- Flexibel verbunden: Erweitere deine PC-Arbeitsfläche mit dem Galaxy Tab A11+ als zweiten Bildschirm und binde es nahtlos in dein Samsung Galaxy Ecosystem ein
Galaxy Tab A11+ 5G (11")
Samsung Galaxy Tab A11+ 5G (11"). Bildschirmdiagonale: 27,9 cm (11"), Display-Auflösung: 1920 x 1200 Pixel. Interne Speicherkapazität: 128 GB. Prozessor-Taktfrequenz: 2 GHz. Speicherkapazität: 6 GB. Auflösung Rückkamera (numerisch): 8 MP, Auflösung Frontkamera (numerisch): 5 MP, Frontkamera. Top WLAN-Standard: Wi-Fi 5 (802.11ac). Integrierter Kartenleser. Gewicht: 482 g

Bildschirm		Netzwerk	
Bildschirmdiagonale *	27,9 cm (11")	Dual-SIM Unterstützung	✗
Display-Auflösung *	1920 x 1200 Pixel	Anschlüsse und Schnittstellen	
Panel-Typ *	TFT	Kopfhörer-Anschluss	3,5 mm
HD-Typ	WUXGA	Design	
Anzahl der Farben des Displays	16 Millionen Farben	Formfaktor *	Tablet
Prozessor		Leistungen	
Anzahl Prozessorkerne	8	GLONASS	✓
Prozessor Boost-Frequenz	2,5 GHz	BeiDou	✓
Prozessor-Taktfrequenz *	2 GHz	GPS	✓
Speicher		Galileo	✓
Speicherkapazität *	6 GB	Quasi-Zenit-Satelliten-System (QZSS)	✓
Speichermedium		Beschleunigungsmesser	✓
Interne Speicherkapazität *	128 GB	Umgebungslichtsensor	✓
Integrierter Kartenleser *	✓	Gyroskop	✓
Kompatible Speicherkarten	MicroSD (TransFlash)	Hallsensor	✓
Max. Speicherkartengröße	2 TB	Software	
Kamera		Plattform *	Android
Auflösung Rückkamera (numerisch) *	8 MP	Akku/Batterie	
Autofokus	✓	Akku-/Batteriekapazität *	7040 mAh
Rückkamera-Blitz	✗	Austauschbare Batterie	✗
Frontkamera *	✓	Kontinuierliche Videowiedergabe	15 h
Auflösung Frontkamera (numerisch)	5 MP	Gewicht und Abmessungen	
Netzwerk		Breite	257,1 mm
Bluetooth-Version	5.3	Tiefe	6,9 mm
Top WLAN-Standard *	Wi-Fi 5 (802.11ac)	Höhe	168,7 mm
Wi-Fi Direct	✓	Gewicht	482 g
Nahfeldkommunikation (NFC)	✗	Sonstige Funktionen	
Begriff der Sicherheitsaktualisierung 30 November 2032			

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 17-NOV-2025. Prints or copies of Information are only valid on the printed Publication date