

PATH TO THE FUTURE



Picture and logos

SELLING POINTS

- Windows 11 Home/Windows 11 Pro(MSI empfiehlt Windows 11 Pro für Unternehmen.)
- Bis zu Intel® Core™ Ultra 9 Prozessor 285K mit NPU
- NVIDIA GeForce RTX 50 Serie Grafikkarten
- AI HMI - Der Touchscreen sorgt für eine intuitive Bedienung und lässt sich mit den exklusiven AI-Apps von MSI für erweiterte AI-Funktionen synchronisieren.
- AI Gaming Desktop-PC - KI-gesteuerte Verbesserungen bei Kühlung, Gaming und Game-Streaming
- Silent Storm Cooling AI - Optimierte den Luftstrom durch Anpassung der Lüftergeschwindigkeiten mit AI-Algorithmen
- 360mm AIO Wasserkühlung - Führt die Wärme von High-End-CPU's effizient ab
- Glacier Armor - Die Kühlkörper an RAM, SSD, PCH und VRM verringern die Wärmeentwicklung.
- PCIe 5.0 SSD - Lade deine Spiele in Sekundenschnelle
- 8pin Power Connector - Zusätzlicher Onboard-PCIe-Stromanschluss sorgt für anhaltende GPU-Leistung für AI-Computing-Aufgaben
- Einfach aufzurüsten - Die Komponenten lassen sich mühelos aufrüsten
- Mystic Light RGB-LED-Design zur individuellen Gestaltung deines Gaming-PCs
- Die transparente Seitenwand erfüllt die EMI-Norm
- 5G LAN & WiFi 7 Technik - Gaming-Erlebnis ohne Verzögerung



1. 1x USB 10Gbps Typ C
2. 1x USB 5Gbps Typ A
3. 1x Kopfhörerausgang
4. 1x Mikrofoneingang
5. 2x USB 2.0 Typ A / 1x PS/2
6. 2x USB 5Gbps Typ A / 2x USB 2.0 Typ A
7. Flash BIOS port
8. 1x USB 10Gbps Typ C / 1x USB 10Gbps Typ A / 1x RJ45 (5G LAN)
9. 2x Wi-Fi Antenne
10. 3x Audioanschlüsse



DESKTOP

MEG Vision X AI 2nd

MEG VISION X AI 2-285AT

SPECIFICATION

Betriebssystem	Betriebssystem	Windows 11 Home
Prozessor	CPU Number	Intel Core Ultra 9 processor 285K
	CPU Clock	3.7GHz
	CPU Cores	24
	TDP	125W
	Cache	36 MB Intel® Smart Cache
	Threads	24
	Max Turbo Frequency	up to 5.70 GHz
	CPU Cooler	Liquid cooling
	Platform TOPS	N/A
	NPU TOPS	N/A
Chipsatz	Chipsets	Z890
Grafik	GPU1 VRAM Size	16G
	VGA I/O Port	HDMIx1, Display Portx3
	GPU1 Vendor	NVIDIA
	GPU1 MKT Name	GeForce RTX 5080
Arbeitsspeicher	Memory Size	64GB(32GB*2)
	Memory Type	DDR5 SDRAM
	Module Type	U-DIMM
	Memory Slot (Total/Free)	4/2
	Max Capacity	Max 128GB
Speicher	SSD Interface	PCIe GEN4x4
	SSD Form Factor	M.2-2280 M-KEY
	SSD Config	1TB*1
	SSD Size	1TB
	HDD1 Interface	N/A
	HDD1 Form Factor	N/A
	HDD1 Size	N/A
	HDD1 RPM	N/A
	ODD(Type)	N/A
	ODD Height	N/A
	ODD Type	N/A
	M.2 slots (Total/Free)	3/2
	2.5" Drive Bays (Total/Free)	1/1
	3.5" Drive Bays (Total/Free)	1/1
Audio	Audio Chipset	Realtek ALC1220P
	Audio Type	7.1 Channel HD Audio
	D-MIC	1
Kommunikation	LAN	Intel Killer E5000
	WLAN Version	Wi-Fi 7+BT
	BT Version	5.4
	WLAN	INTEL/BE200.NG.WG.NVX
Schnittstellen (Vorne)	Audio Mic-in	1
	Audio Headphone-out	1
	USB 3.2 Gen 2 (10G) Type C	1
	USB 3.2 Gen 1 (5G) Type A	2
	Copilot Button	N/A
Schnittstellen (Rückseite)	Thunderbolt (R)	2x (Thunderbolt 4)
	RJ45	1
	WiFi Antenna	2
	Audio jack	2
	S/PDIF	1
	USB 3.2 Gen 2x2 (20G) Type C (R)	1
	USB 3.2 Gen 2 (10G) Type A (R)	3
	USB 3.2 Gen 1 (5G) Type A (R)	4
	Lock type	Kensington Lock
Power	Power	850W
	Power Certification	80PLUS GOLD
	Formfactor	ATX
	Type	POWER SUPPLY



DESKTOP

MEG Vision X AI 2nd

MEG VISION X AI 2-285AT

Abmessungen & Gewicht	Product Dimension (WxDxH) (mm)	502.7 x 299.3 x 423.4
	Product Dimension (WxDxH) (inch)	19.79 x 11.78 x 16.67
	Inside Carton Dimension (WxDxH) (mm)	N/A
	Inside Carton Dimension (WxDxH) (inch)	N/A
	Outer Carton Dimension Standard (WxDxH) (mm)	N/A
	Outer Carton Dimension Standard (WxDxH) (inch)	N/A
	Weight (Net kg)	18.225
	Net Weight (lbs)	40.18
	Weight (Gross kg)	23.189
	Gross Weight (lbs)	51.12
	Liter	42.6
	Pint	90.03
Lagerung & Zertifikationen	Operating, Storage Temperature	0° C ~ 35° C ; -20° C ~ 60° C
	Operating, Storage Humidity	0% ~ 85%;0% ~ 90%
	Regulatory Compliance	BSMI, CB/CE, FCC(Class B), RCM(C-Tick), UL(CUL), VCCI
Garantie	Warranty	36months
Zubehör	Keyboard Interface	N/A
	Mouse Interface	N/A
	Power Cord	1
	AC Adaptor	N/A
	Warranty Card	N/A
	Quick Guide	4
	User Manual	N/A
	VESA Mount kit	N/A
	Keyboard	N/A
	Mouse	N/A
	Power Switch	N/A
Barcode Info	EAN	4711377432207
Model	Part No	9S6-B92111-285
	MKT Name	MEG Vision X AI 2
	MKT Spec	MEG Vision X AI 2-285AT
	Color	ID1/Black-Black-Black
	Model	B921
Security	TPM module	N/A
	Chassis Lock	N/A
	Chassis Intrusion	N/A