

WB-Camp

2/3/4/5G

LTE/GPRS/UMTS-Antenne 2/5dBi 617-4200MHz 0,35 m SMA-Stecker

Frequenzen: 617-960 / 1710-4200MHz

Gewinn: @617-960MHz 2dBi

@1710-2700 MHz 3.5dBi

@3300-4200MHz 5dBi maximal

Polarisation: Vertikal

Strahlungsmuster: Omni-Direktional

Widerstand: 50 OHM

max. Eingangsleistung: 60W

Maße: Höhe 100x100x320mm

Material: ABS Kunststoff

Farbe: Weiß

Befestigung: Wandmontage/ Mastmontage/ Tischmontage

Kabeltyp: SR1-029-B

Kabellänge: 0,35m

Stecker: SMA-Stecker



5G



Product		WB-Camp für LTE 5G	
Product code		A741009	
Product type		communication antenna	
Type		SISO antenna	
Cable	length	m	0,35
	no. of cables		2
	cable type		-
Connector	type		SMA
	number		2
Applications		GSM/DCS/3G/LTE/WLAN/5G	
Manufacturer		Danitech	
Brand		WB-Camp	
Applications		Outdoor	
Operating band	MHz	617-960, 1710-2700, 3300-4200	
Max. gain	dBi	5	
Impedance	Ω	50	
Radiation angle	vertical polarization	H/V°	617-960 MHz:85 , 17102700 MHz:70, 33004200 MHz: 55
	horizontal polarization	H/V°	-
Polarization		V	
DC-shorted		Yes	
VSWR		<2.5	
Max. mast diameter	mm	50	
Dimensions	mm	φ82*800	
Packaging		cardboard box	
Dimensions	mm	100x100x320	Weight: 0,800 kg

Artikelnummer 103562

