

Dabman 280CDWDSI

DAB+/FM radio with CD player, USB and Bluetooth



Automatic
Safety Alert



2 X
15W
RMS

425MM

135MM



EN

- DAB+
- ASA (Automatic Safety Alert)
- CD MP3 player
- Bluetooth 5.4
- PLL FM radio
- Dual alarm function
- LCD + Dot matrix display
- Multiple OSD languages
- Audio formats: MP3, WAV, AAC
- Output power: 2 x 15 Watt (RMS)
- 2 x VU meters
- Equalizer
- USB player, USB charger
- Telescopic antenna
- Connections: Aux input, 3,5mm earphone jack, 2 x USB, RCA AUX-IN
- Included: Remote control, AC Adaptor, RCA cable, 3,5mm line in cable

DE

- DAB+
- ASA (Automatic Safety Alert)
- CD/MP3-Player
- Bluetooth 5.4
- PLL FM Radio
- Zwei Weckzeiten
- LCD + Dot matrix-Display
- Mehrere OSD-Sprachen
- Audioformate: MP3, WAV, AAC
- Ausgangsleistung: 2 x 15 Watt (RMS)
- 2 x VU-Messgeräte
- Equalizer
- USB-Spieler, USB-aufladen
- Teleskopantenne
- Anschlüsse: AUX-Eingang 3,5 mm, 3,5 mm Kopfhörerbuchse, 2 x USB, RCA AUX-in
- Inklusiv: Fernbedienung, Netzadapter, RCA-Kabel, Line-Eingang 3,5mm Kabel

NL

- DAB+
- ASA (Automatic Safety Alert)
- CD/MP3 speler
- Bluetooth 5.4
- PLL FM radio
- Dubbel alarm
- LCD + dot matrix scherm
- Meerdere OSD talen
- Ondersteunde audio formaten: MP3, WAV, AAC
- Uitgangsvermogen: 2 x 15 Watts (RMS)
- 2 x VU-meter
- Equalizer
- USB-speler, USB lader
- Telescopische antenne
- Aansluitingen: AUX ingang van 3,5 mm, 3,5 mm hoofdtelefoon uitgang, 2 x USB, RCA AUX-in
- Inclusief: Afstandsbediening, AC-adapter, RCA kabel, 3,5mm line ingang kabel

FR

- DAB+
- ASA (Automatic Safety Alert)
- Lecteur CD/MP3
- Bluetooth 5.4
- Radio FM avec tuner PLL
- Fonction double alarme
- Écran LCD + dot matrix
- Affichage multi-langues
- Formats audio supportés: MP3, WAV, AAC
- Puissance de sortie: 2 x 15 Watts RMS
- 2 x VU-mètres
- Égaliseur
- Lecteur USB, Chargeur USB
- Antenne télescopique
- Connexions: Entrée AUX de 3,5 mm, Prise casque 3,5 mm, 2 x USB, RCA AUX-in
- Inclus: Commande à distance, Adaptateur AC, Câble RCA, Câble Entrée line de 3,5 mm

ES

- DAB+
- ASA (Automatic Safety Alert)
- Reproductor de CD/MP3
- Bluetooth 5.4
- Radio FM PLL
- Función alarma dual
- Pantalla de LCD + matriz de puntos
- Idiomas multiples OSD
- Formatos audio: MP3, WAV, AAC
- Potencia de salida: 2 x 15 Watt (RMS)
- 2 vúmetros
- Ecualizador
- USB reproduce, Cargador USB
- Antena telescópica
- Conexiones: Entrada AUX 3,5 mm, jack para auriculares de 3,5mm, 2 x USB, RCA AUX-in
- Incluye: Mando a distancia, Adaptador CA, Cable RCA, Cable Entrada Line 3,5mm

DATA :

- Power source: AC 100-230V~50Hz
- Power consumption max: 30W
- Remote control battery: 2 x AAA (not included)
- Dim. unit: 425 x 308 x 135mm (WxDxH)
- Gift box Dim.: 465 x 365 x 190mm (WxDxH)
- Net/Gross Weight: 4,67 kg / 5,99 kg
- Master carton quantity: 1pcs
- EAN-code: 8711902091806
- Custom code: 8527910000
- Container quantity:
- 20' ft : 750pcs
- 40' ft : 1560pcs
- 40'HQ : 1870pcs

Subject to changes without prior notice

