





LT Soldering Tip Family

- + Designed for universal applications
- + Universal SMT & THT jobs
- + A wide range of low cost tips
- + Solid copper plated with iron for maximum durability and long life



Chisel  	Article LT 1SC T0054449499  0.4 mm / 0.15 mm 0.016 inch / 0.006 inch	Article LT B T0054440599 BESTSELLER  2.4 mm / 0.8 mm 0.094 inch / 0.031 inch	Article LT HX T0054442099  0.8 mm / 0.4 mm 0.031 inch / inch	
	LT 1SCNW T0054449799  0.3 mm / 0.1 mm 0.012 inch / 0.004 inch	LT BSL T0054451799  2.4 mm / 0.45 mm 0.094 inch / 0.018 inch	LT K T0054443899 BESTSELLER  1.2 mm / 0.4 mm 0.047 inch / 0.016 inch	
	LT 4X T0054442899  1.2 mm / 0.4 mm 0.047 inch / 0.016 inch	LT BX T0054444299  2.4 mm / 0.8 mm 0.094 inch / 0.031 inch	LT L T0054441499  2.0 mm / 1.0 mm 0.079 inch / 0.034 inch	
	LT A T0054444099 BESTSELLER  1.6 mm / 0.7 mm 0.063 inch / 0.028 inch	LT C T0054440799  3.2 mm / 0.8 mm 0.126 inch / 0.031 inch	LT M T0054442599  3.2 mm / 1.2 mm 0.126 inch / 0.047 inch	
	LT ALX T0054444399  1.6 mm / 0.7 mm 0.063 inch / 0.028 inch	LT D T0054440999  4.6 mm / 0.8 mm 0.181 inch / 0.031 inch	LT MX T0054446999  3.2 mm / 1.2 mm 0.126 inch / 0.047 inch	
	LT ASL T0054451699  1.6 mm / 0.45 mm 0.063 inch / 0.018 inch	LT DLL T0054444899  4.6 mm / 1.2 mm 0.181 inch / 0.047 inch	LT MX2 T0054451299  3.0 mm / 1.0 mm 0.118 inch / 0.034 inch	
	LT AX T0054442799  1.6 mm / 0.8 mm 0.063 inch / 0.031 inch	LT H T0054443799 BESTSELLER  0.8 mm / 0.4 mm 0.031 inch / 0.016 inch		

Conical long  	LT 1L T0054442399  0.2 mm 0.008 inch	LT O T0054448199  0.8 mm 0.031 inch	
	LT 1LNW T0054449899  0.1 mm 0.004 inch	LT S T0054440699  0.4 mm 0.016 inch	
	LT 1LX T0054442499  0.2 mm 0.008 inch	LT T T0054448299  0.6 mm 0.024 inch	

Silver Line



Heat up time

°C

350

300

200

100

0

10 Sec.*


Component size



S

 TO

M

*from 50°C to 350°C / 120°F to 620°F

Round  	Round	LT 1 T0054443599  0.25 mm 0.01 inch	Round tip sloped 45° LT 4 T0054443999  1.2 mm 0.047 inch
	LT 1A T0054448999  0.5 mm 0.02 inch	LT BB 45 T0054448499  2.4 mm 0.094 inch	
	LT 1S T0054443699 BESTSELLER  0.2 mm 0.008 inch	LT DD 45 T0054447899  4.0 mm 0.157 inch	
	LT 1SA T0054448899  0.5 mm 0.02 inch	LT DD 45 T0054448699  4.6 mm 0.181 inch	
	LT 1SNW T0054449699  0.1 mm 0.004 inch	LT F T0054440899  1.2 mm 0.047 inch	
	LT 1X 30° T0054442599  0.4 mm 0.016 inch	LT 22CP T0054440873  2.0 mm 0.079 inch	
	LT AS T0054440499  1.6 mm 0.063 inch	LT 33CP T0054440877  3.0 mm 0.118 inch	
	LT BS T0054449999  2.0 mm 0.079 inch	Round sloped 60°	
	LT CS T0054441199  3.2 mm 0.126 inch	LT AA 60° T0054448799  1.6 mm 0.063 inch	

Measuring tip	LT Measuring tip T0054441699  0.5 mm 0.02 inch	Gullwing  	LT GW1 T0054441099  1.4 mm 0.055 inch
Adapter	LT Adapter T0054412199  LT Screw in tip M4 T005444499 		LT GW2 T0054451199  3.5 mm 0.138 inch

Weller®

weller-tools.com/toolselector/en
weller-tools.com/toolselector/us