

	Model	load(%)	load(W)	Backup time
	DN-170130	25%	250	24'28"
		50%	500	10'56"
		75%	750	5'20"
		100%	1000	2'41"
	DN-170131	25%	500	28'4"
		50%	1000	11'
		75%	1500	5'37"
		100%	2000	2'55"
	DN-170132	25%	750	24'20"
		50%	1500	10'42"
		75%	2250	5'36'
		100%	3000	3'26"