

## Datenblatt Art. 398.182

Data sheet | Fiche technique | Scheda tecnica | Fișa tehnică

### Kabeltrommel 4-fach

| Elektrische Kenngrößen                |                                      | Electrical parameters                |                                      |
|---------------------------------------|--------------------------------------|--------------------------------------|--------------------------------------|
| <b>Nennstrom / Bemessungsspannung</b> | 16A / 250V~                          | <b>Rated current / rated voltage</b> | 16A / 250V~                          |
| <b>Frequenz</b>                       | 50 Hz                                | <b>Frequency</b>                     | 50 Hz                                |
| Netzanschluss                         |                                      | Power supply                         |                                      |
| <b>Zuleitung</b>                      | 50m   H05RR-F   3G1,5mm <sup>2</sup> | <b>Supply cable</b>                  | 50m   H05RR-F   3G1,5mm <sup>2</sup> |
| Farbe Zuleitung                       | Schwarz                              | Colour supply cable                  | Black                                |
| <b>Stecker</b>                        | CEE 7/7 (Type E/F)                   | <b>Plug</b>                          | CEE 7/7 (Type E/F)                   |
| Stromausgang                          |                                      | Power output                         |                                      |
| <b>Steckdosen</b>                     |                                      | <b>Socket outlets</b>                |                                      |
| <b>4x CEE 7/3 (Type F)</b>            |                                      | <b>4x CEE 7/3 (Type F)</b>           |                                      |
| 2-polig mit Schutzkontakt             |                                      | 2-pole with earthing contact         |                                      |
| Schwarz, ähnlich RAL 9005, 35°        |                                      | Black, similar to RAL 9005, 35°      |                                      |
| 16A / 250V~, IP20                     |                                      | 16A / 250V~, IP20                    |                                      |
| Schutzeinrichtungen                   |                                      | Protective devices                   |                                      |
| <b>Thermoschutzschalter</b>           | 1-polig, rückstellbar                | <b>Thermo protection switch</b>      | 1-pole, resettable                   |
| Weitere Produkteigenschaften          |                                      | Further product attributes           |                                      |
| <b>Abmessungen</b>                    | 280x190x380mm                        | <b>Dimensions</b>                    | 280x190x380mm                        |
| <b>Durchmesser</b>                    | 285mm                                | <b>Diameter</b>                      | 285mm                                |
| <b>Material</b>                       | Stahlblech, silber                   | <b>Material</b>                      | Sheet steel, silver                  |
| <b>Lieferumfang</b>                   | 1x Kabeltrommel 4-fach ohne Deckel   | <b>Scope of delivery</b>             | 1x Cable reel 4-way without lid      |
| Im Karton                             |                                      | In carton                            |                                      |
| Umgebungsbedingungen                  |                                      | Environmental conditions             |                                      |
| <b>Schutzart</b>                      | IP20                                 | <b>Protection type</b>               | IP20                                 |

