

3D-VIDEO BORESCOPE

PCE-VE 1600-3D



Specification

General technical data	
cable length	3 m
Display Typ	LCD touchscreen
Display size	7 in
Display resolution	One thousand nine hundred twenty by one thousand two hundred
Storage medium	Internal memory, SD card
Storage capacity	16 GB
Memory capacity Additional information	SD card up to 128 GB possible
Interface	Mini-HDMI, USB-C, USB, 3.5 mm jack, WLAN
Camera resolution	1000000 pixels
Resolution	Image: 1280x720 Video: 1280x720
Operating time	4 h
Camera head diameter	6 mm
Camera probe material	Braided tungsten
Camera probe movement	360 °
Protection class camera probe	IP67
Temperature range of camera probe	-25 ... 80 °C
Field of vision	120 °
Depth of field of vision	10 ... 100 mm
Bend angle	190 °
Luminous intensity	50000 lx
Picture / Video format	PNG
Menu language	German, English (GB), English (US), French, Italian, Russian, Spanish, Polish, Korean, Japanese, Chinese
Protection class (device)	IP65
Power supply	100 to 240V AC (power supply unit)
Connector type	Euro plug
Battery/battery	1 x 7,4 battery pack , Lithium-ion battery
Battery capacity	6400 mAh
Operating conditions	-15 ... 50 °C , 0 ... 92 %RH
Storage conditions	-23 ... 63 °C , 0 ... 92 %RH
Dimensions (L x W x H)	370 x 195 x 150 mm
Weight	1013 g