# bea-fon SL645 LTE
SILVER LINE

© Bea-fon Mobile GmbH | 17.02.2026

www.beafon.com
info@beafon.com

SL645 LTE




IP 54 | 4G VoLTE | SMS/MMS | Display 2.8" 1.77" | Camera | Light Signal | SOS Key | Silent Alarm | 123 | Torch | Calculator | Hands-free | Calendar | FM Radio | USB Type - C

## Funktionen
- XXL 2,8" (7,11cm) Farbinnendisplay
- XXL 1,77"(4,49cm) Farbaußendisplay
- Kamera
- Fotokontaktanzeige
- Extra große beleuchtete Tasten
- Tastenansage der Nummern zuschaltbar
- Extra große XXL Zahlen im Displayanzeige
- Leichte Menüführung
- Extral lauter Klingelton
- Taschenlampe
- Bluetooth
- Freisprechen
- SOS Taste auf der Geräterückseite
- SOS Nummern frei programmierbar
- SMS / MMS
- Tischladeschale im Lieferumfang

## Functions
- XXL 2.8 "(7.11cm) color interior display
- XXL 1.77 "(4.49cm) color exterior display
- Camera
- Photo contact
- Extra large illuminated keys
- Number keys Voice tone
- Extra large XXL numbers in the display
- Easy menu navigation
- Extra loud ringtone
- Flashlight
- Bluetooth
- Hands-free
- SOS button on the back of the device
- SOS numbers freely programmable
- SMS / MMS
- Desktop charger included

## Les fonctions
- Écran intérieur couleur XXL de 7,11 cm (2,8 po)
- Écran extérieur couleur XXL de 4,49 cm (1,77 po)
- Caméra de haute
- Contact photo
- Touches lumineuses extra larges
- Touches numériques Tonalité
- Chiffres XXL extra-larges à l'écran
- Navigation facile dans les menus
- Sonnerie extra forte
- Lampe de poche
- Bluetooth
- Mains libres
- Bouton SOS à l'arrière de l'appareil
- Numéros SOS librement programmables
- SMS / MMS
- Chargeur de bureau inclus

## Funzioni
- Display interno a colori TFT da 2,8" ad alto contrasto
- Display esterno a colori TFT da 1,77" ad alto contrasto
- Fotocamera
- Foto del contatto
- Display esterno per i messaggi di stato
- Tasti numerici Tono di voce
- Tasto della fotocamera
- Tasto per chiamate di emergenza SOS
- Alloggiamento di ricarica da tavolo incluso nella confezione
- Torcia
- Bluetooth
- Suoneria ad alto volume
- Tasti illuminati di grandi dimensioni
- SMS / MMS
- Caricatore da tavolo incluso

# bea-fon SL645 LTE
SILVER LINE

**EAN Black: 9120124824144**
**Art.-Nr. Black: SL645LTE_BE003B**

**EAN Black: 9120124824557**
**Art.-Nr. Black: SL645LTE_EU003B**

| Specifications | |
|---|---|
| Type | Clamshell phone |
| Colour | Black silver |
| Dimensions in mm (L x W x D) | 114,8x60x19,1 |
| Weight in grammes | 120 |
| Standby time in hours | 250 |
| Talk time in minutes | 200 |
| Battery | Li-ion 3.7V - 1550mAh |
| USB Type-C | ✓ |
| Network 2G | 800 / 1900 |
| Network 3G | 2100 |
| Network 4G | B1/B3/B7/B8/B20 |
| SAR head | 0.75 W/kg |
| SAR body | 1.62 W/kg |
| SIM card | Nano |
| Backlit keypad | ✓ |

| Safety functions | |
|---|---|
| Unique emergency call key | ✓ |
| Extra loud ringtone | ✓ |
| Torch | ✓ |
| Speed dial keys (2-9) | ✓ |
| Direct dial keys (M1/M2) | ✓ |
| Light signal for incoming calls or messages | ✓ |

| Display | |
|---|---|
| Mono/Colour | TFT colour |
| Colours | 65,000 |
| Resolution | 240 x 320 |
| Size | 2.8" |
| External display type | TFT colour display |
| External display resolution | 128*160 |
| External display type | 1.77 |
| Extra large font | ✓ |
| Clock | ✓ |
| Date | ✓ |

| Tones and signals | |
|---|---|
| Profile | ✓ |
| Polyphonic ringtones | ✓ |
| Extra loud ringtone | ✓ |
| Vibration alarm | ✓ |
| Turn keypad tone on/off | ✓ |
| Key signal tone of numbers | ✓ |

| SOS settings | |
|---|---|
| SOS key | ✓ |
| SOS SMS | ✓ |
| SOS numbers | 5 |
| SOS sound alarm | ✓ |

| Call | |
|---|---|
| Phone numbers in phonebook | 250 |
| Volume settings | 7 |
| Hands-free function | ✓ |
| Speaker volume control | ✓ |
| Headset port | 3.5 jack |
| Mute | ✓ |
| Call duration | ✓ |
| Conference call | ✓ |

| Call list | |
|---|---|
| Incoming calls | 20 |
| Missed calls | 20 |
| Dialled calls | 20 |
| Call duration | ✓ |


| SMS / MMS | |
|---|---|
| Send | ✓ |
| Receive | ✓ |
| Call back | ✓ |
| Send to selected receivers | ✓ |
| Delete | ✓ |
| Delete all messages | ✓ |
| Forward messages | ✓ |
| Text mode / Smart input method | Abc, ABC, abc, 123 |

| Network services | |
|---|---|
| Caller ID | ✓ |
| Call waiting | ✓ |
| Forward (all) calls | ✓ |
| Forward call if not reachable | ✓ |
| Forward call if not answered | ✓ |
| Forward call if busy | ✓ |
| Forward (all) data | ✓ |
| Manual/automatic network selection | ✓ |

| Safety | |
|---|---|
| Lock phone | ✓ |
| Turn SIM PIN on/off | ✓ |
| Change SIM PIN | ✓ |
| Reset to default settings | ✓ |

| Extras | |
|---|---|
| Phone languages | EN/FR/HU/PT/ES/IT/ TR/DE/CZ/SL/HR/RO/ NL/FI/SV/NO/DA/SK/PL |
| User guide languages | EN/FR/HU/PT/ES/IT/ TR/DE/CZ/SL/HR/RO/ NL/FI/SV/NO/DA/SK/PL |
| Protection class | IP54 |
| Alarm | ✓ |
| Calendar | ✓ |
| Reminders | ✓ |
| Calculator | ✓ |
| FM radio | ✓ |
| Bluetooth | ✓ |
| Photo contact | 8 |
| Camera | 1.3MP |
| Micro SD card slot | Up to 64GB |

| Standard package contents EU | |
|---|---|
| Mobile phone | ✓ |
| Battery | ✓ |
| Desktop cradle | ✓ |
| Cable USB Typ-C | ✓ |
| User guide | DE |
| Quick guide | FR / IT / NL / EN |




Advance data sheet!
Note:
The figure and technical data do not yet correspond to the original.

www.beafon.com
info@beafon.com

© Bea-fon Mobile GmbH | 17.02.2026