BUSINESS PRODUCTIVITY MONITOR

PRO MP341CQPHG E12

PRO MP341CQPHGN E12

Business & Productivity Monitor

Der PRO MP341CQPHG E12 ist der beste 21:9 UWQHD Curved Monitor für Multitasking. Seine ultra-breite Bildschirmgröße ermöglicht es den Benutzern, immer alles im Blick zu haben. Der 1500R gebogene Bildschirm und die 120Hz Flicker-Free-Technologie tragen zu einem optimalen Seherlebnis bei.



Picture and logos

SELLING POINTS

- 21:9 UWQHD-34"-Bildschirm verbessert Multitasking und erweitert Ihren Horizont.
- Die 1500R-Krümmung sorgt für ein besonders immersives Seherlebnis bei der Arbeit und im Alltag.
- Type-C 98 W Stromversorgung sowie Display- und KVM-Switch.
- Genießen Sie hochwertige Unterhaltung mit einer flüssigen Bildwiederholrate von 120 Hz.
- Das TÜV-zertifizierte Display schont Ihre Augen.
- Die MSI EyesErgo-Technik mit Anti-Flicker-Technik hilft, Augenbelastungen und Ermüdungserscheinungen vorzubeugen.
- MSI Eye-Q Check hilft dir dabei, deine Augen selbst zu überprüfen und erinnert dich daran, bei längerer Nutzung des Monitors Pausen einzulegen.
- Genieße eine aufgeräumte Umgebung dank praktischem und abnehmbarem Kabelmanagement und Standard-Vesa Design.
- MSI Power Link ermöglicht das Einschalten Ihres MSI-Desktops mit einem einzigen Druck auf den Netzschalter des Monitors.
- Mit mehreren Eingangsquellen wie HDMI™- und DP-Anschlüssen sind Sie für alles gerüstet, was Sie brauchen
- Zwei eingebaute Lautsprecher.



1. 5 Wege Joysticknavigation
2. Stromanschluss
3. Kopfhöreranschluss
4. 1x HDMI™ 2.0b (UWQHD@120Hz) + 1x DisplayPort 1.4a
5. Typ-C (DP alt.) mit 98W PD
6. 1x USB 5Gbps Typ-B
7. 4x USB 5Gbps Typ-A
8. Kensington Lock

"2026-10-23 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products."

BUSINESS PRODUCTIVITY MONITOR

PRO MP341CQPHG E12

PRO MP341CQPHGN E12

SPECIFICATION

Model	SKU Number	PROMP341CQPHGNE12
	Entity MKT Name	PRO MP341CQPHGN E12
	Part No	9S6-3PFA9T-001
	Color	ID1/Black-Black
Display	Screen Size	34" (86.36 cm)
	Active Display Area (mm)	797.22(H) x 333.72(V)
	Curvature	Curve 1500R
	Panel Type	VA
	Resolution	3440x1440 (UWQHD)
	Pixel pitch (mm)	0.23175(H)x0.23175(V)
	Aspect Ratio	21:9
	Dynamic Refresh Rate technology	AMD FreeSync™ Premium
	Dynamic Refresh Rate Activated Range	48~120Hz
	HDR (High dynamic range)	HDR Ready
	SDR Brightness (nits)	300
	Contrast Ratio	3500:1
	DCR (Dynamic Contrast Ratio)	100000000:1
	Signal Frequency	70.6~176.4 KHz(H) / 48~120 Hz(V)
	Refresh Rate	120Hz
	Response Time (MPRT)	1ms(MPRT)
	Response Time (GTG)	4ms
	View Angles	178°(H)/178°(V)
	NTSC (CIE1976 area percentage/overlap)	100%/86%
	NTSC (CIE1931 area percentage/overlap)	86%/80%
	sRGB (CIE1976 area percentage/overlap)	114%/98%
	sRGB (CIE1931 area percentage/overlap)	121%/99%
	Adobe RGB (CIE1976 area percentage/overlap)	98%/89%
	Adobe RGB (CIE1931 area percentage/overlap)	90%/84%
	DCI-P3 (CIE1976 area percentage/overlap)	91%/91%
	DCI-P3 (CIE1931 area percentage/overlap)	90%/90%
	Rec.709 (CIE1976 area percentage/overlap)	114%/98%
	Rec.709 (CIE1931 area percentage/overlap)	121%/99%
	Rec.2020 (CIE1976 area percentage/overlap)	66%/66%
	Rec.2020 (CIE1931 area percentage/overlap)	64%/64%
	Surface Treatment	Anti-glare
	Display Colors	1.07B
	Color bit	10 bits (8 bits + FRC)
Schnittstellen	USB Type C (DisplayPort Alternate)	1
	Headphone-out	1
	USB 3.2 Gen 1 Type A	4
	USB 3.2 Gen 1 Type B	1
	Lock type	Kensington Lock
	Speaker	2Wx 2
	HDMI	1
	HDMI version	2.0b
	HDMI HDCP version	2.3
	DisplayPort	1
	DisplayPort version	1.4a (HBR3)
	DisplayPort HDCP version	2.3
Garantie	Warranty	36M
Power	Power Type	Internal Power Board
	Power Input	100~240V, 50/60Hz
	On-mode Power Consumption (KWh/1000h)	SDR : 25 / HDR : 50
	Annual Energy Consumption (KWh)	44
	Standby-mode Power Consumption (W)	0.5
	Off-mode Power Consumption (W)	0.3
	Energy Efficiency Rating	E (SDR) G (HDR)
	Power Cord Type	C13

"2026-10-23 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products."

PRO MP341CQPHG E12

PRO MP341CQPHGN E12

Zubehör	DisplayPort Cable	1
	HDMI Cable	1
	DVI Cable	0
	USB Type A to Type B Cable	1
	USB Type C to Type A Cable	0
	USB Type C to Type C Cable	1
	Thunderbolt Cable	0
	VGA Cable	0
	3.5mm audio Cable	0
	3.5mm combo audio Cable	0
	3.5mm Mic Cable	0
	Power Cord	1
	AC Adaptor	0
	Quick Guide	1
	Warranty Card	0
	Mouse Bungee Unit	0
Design	Adjustment (Tilt)	-5° ~ 20°
	Adjustment (Swivel)	-45° ~ 45°
	Adjustment (Height)	0 ~ 150 mm
	Adjustment (Pivot)	-10° ~ 10°
	VESA Mounting	100x100mm
Abmessungen & Gewicht (Product)	Product Dimension with Stand (WxDxH) (mm)	809.3 x 234.9 x 549.7
	Product Dimension without Stand (WxDxH) (mm)	809.3 x 112.8 x 365.8
	Stand Dimension (WxDxH) (mm)	300 x 234.9 x 411.5
	Weight (Net kg)	9.
	Weight Without Stand (kg)	6.2
Abmessungen & Gewicht (Verpackung)	Inside Carton Dimension (WxDxH) (cm)	98.5 x 17.1 x 51.3
	Outer Carton Dimension (WxDxH) (cm)	100 x 18.6 x 53.6
	Weight (Gross kg)	12.3
Barcode Info	EAN	4711377421928

“2026-10-23 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products.”