BUSINESS PRODUCTIVITY MONITOR

PRO MP273UPDE E6

PRO MP273UP E6

Be Your Window To The World



Picture and logos

SELLING POINTS

- 27"-Display mit UHD (2160p)-Auflösung für Programmierung, Videobearbeitung und Webdesign.
- TÜV-zertifiziertes Display schützt deine Augen.
- Die MSI EyesErgo-Technik mit Anti-Flicker hilft, Augenbelastung und Ermüdung vorzubeugen.
- MSI Eye-Q Check hilft dir, deine Augen selbst zu überprüfen und erinnert dich daran, bei langer Nutzung eine Pause einzulegen.
- PIP-/PBP-Modi bieten Creator bei Bedarf mehr Effizienz.
- Erhalte Vielseitigkeit über verschiedene Geräte hinweg, indem du mehrere Eingangsquellen wie HDMI™- und DP-Anschlüsse nutzt.
- Genieße eine aufgeräumte Umgebung dank praktischer, abnehmbarer Kabelführung.
- Standard-VESA-Montage und vierfach verstellbares Standfuß-Design.
- Zwei integrierte Lautsprecher.



1. 2x HDMI™ (2.0b)
2. 1x DipslayPort 1.4a
3. 1x Kopfhörerausgang
4. 1x Stromanschluss
5. 1x Kensington Lock
6. OSD Knopf

"2026-10-23 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products."

BUSINESS PRODUCTIVITY MONITOR

PRO MP273UPDE E6

PRO MP273UP E6

SPECIFICATION

Model	Part No	9S6-3PB49H-405
	Color	ID1/Black-Black
Display	Screen Size	27" (68.58 cm)
	Active Display Area (mm)	596.736(H) x 335.664(V)
	Curvature	Flat
	Panel Type	IPS
	Resolution	3840x2160 (UHD)
	Pixel pitch (mm)	0.1554(H)x0.1554(V)
	Aspect Ratio	16:9
	Dynamic Refresh Rate technology	Adaptive-Sync
	Dynamic Refresh Rate Activated Range	48~60Hz
	HDR (High dynamic range)	HDR Ready
	SDR Brightness (nits)	300
	Contrast Ratio	1000:1
	DCR (Dynamic Contrast Ratio)	100000000:1
	Signal Frequency	110.98~136.68 KHz(H) / 48~60 Hz(V)
	Refresh Rate	60Hz
	Response Time (GTG)	4ms
	View Angles	178°(H)/178°(V)
	NTSC (CIE1976 area percentage/overlap)	113%/90%
	NTSC (CIE1931 area percentage/overlap)	95%/87%
	sRGB (CIE1976 area percentage/overlap)	130%/99%
	sRGB (CIE1931 area percentage/overlap)	136%/99%
	Adobe RGB (CIE1976 area percentage/overlap)	110%/93%
	Adobe RGB (CIE1931 area percentage/overlap)	100%/89%
	DCI-P3 (CIE1976 area percentage/overlap)	103%/98%
	DCI-P3 (CIE1931 area percentage/overlap)	100%/97%
	Rec.709 (CIE1976 area percentage/overlap)	130%/99%
	Rec.709 (CIE1931 area percentage/overlap)	136%/99%
	Rec.2020 (CIE1976 area percentage/overlap)	74%/74%
	Rec.2020 (CIE1931 area percentage/overlap)	70%/70%
	Surface Treatment	Anti-glare
	Display Colors	1.07B
	Color bit	10 bits (8 bits + FRC)
Schnittstellen	Headphone-out	1
	Lock type	Kensington Lock
	Speaker	3Wx 2
	HDMI	2
	HDMI version	2.0b
	HDMI HDCP version	2.3
	DisplayPort	1
	DisplayPort version	1.4a
	DisplayPort HDCP version	2.3
Garantie	Warranty	36M
Power	Power Type	External Adaptor 12V 4A
	Power Input	100~240V, 50/60Hz
	On-mode Power Consumption (KWh/1000h)	26
	Annual Energy Consumption (KWh)	26
	Standby-mode Power Consumption (W)	0.5W
	Off-mode Power Consumption (W)	0.3W
	Energy Efficiency Rating	F
	Power Cord Type	C13

"2026-10-23 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products."

PRO MP273UPDE E6

PRO MP273UP E6

Zubehör	DisplayPort Cable	0
	HDMI Cable	1
	DVI Cable	0
	USB Type A to Type B Cable	0
	USB Type C to Type A Cable	0
	USB Type C to Type C Cable	0
	Thunderbolt Cable	0
	VGA Cable	0
	3.5mm audio Cable	0
	3.5mm combo audio Cable	0
	3.5mm Mic Cable	0
	Power Cord	1
	AC Adaptor	1
	Quick Guide	1
	Warranty Card	0
	Mouse Bungee Unit	0
Design	Adjustment (Tilt)	-5° ~ 20°
	Adjustment (Swivel)	-30° ~ 30°
	Adjustment (Height)	0 ~ 110 mm
	Adjustment (Pivot)	-90° ~ 90°
	VESA Mounting	75x75mm
Abmessungen & Gewicht (Product)	Product Dimension with Stand (WxDxH) (mm)	613.5 x 200.8 x 413.4
	Product Dimension without Stand (WxDxH) (mm)	613.5 x 48.5 x 362.5
	Stand Dimension (WxDxH) (mm)	230.8 x 200.8 x 402.8
	Weight (Net kg)	5.75
	Weight Without Stand (kg)	3.55
Abmessungen & Gewicht (Verpackung)	Inside Carton Dimension (WxDxH) (cm)	84.1 x 13.1 x 44.8
	Outer Carton Dimension (WxDxH) (cm)	85.6 x 14.4 x 47.2
	Weight (Gross kg)	7.75

“2026-10-23 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products.”