1.90.690.864/0000

LED, W2x4.6d, 24 V, 5,8 mm x 5,8 mm, weiß, LED



Beschreibung

Technische Daten

Allgemein

Farbe des Leuchtmittels	weiß
Arbeitstemperatur, min.	-30 °C
Arbeitstemperatur, max.	75 °C
Lagertemperatur, min.	-40 °C
Lagertemperatur, max.	100 °C
beleuchtbar	ja
Leuchtmittel	LED
Leuchtmittelfassung	W 2 x 4,6d
Verpackungseinheit	5 Stück
Nettogewicht	3,8 g
Mindestbestellmenge (MOQ)	5 Stück
RoHS konform	ja
REACH konform	ja

Einbaumaße

Außenmaß Länge	5,8 mm
Außenmaß Breite	5,8 mm
Außenmaß Höhe	18,5 mm

Elektrische Kennwerte

Betriebsspannung des Leuchtmittel, max.	24 V
Nenn-Betriebsspannung	24 V

Direkte Links

RAFI eCatalog

The information in this data sheet only contains general descriptions and / or performance features, which may not apply precisely as described to the respective application, and which may change due to further product enhancements. The technical data, illustrations and other information about our products are the mere results of individual technical testing. These descriptions and other product features are only binding if they expressly agreed upon at the time of the conclusion of a binding contract. In all other cases, we reserve the right to make technical changes as well as changes of availability. Pictures and other graphic illustrations are approximations only. All product names may be trademarks or brand names of the RAFI Group or any other sub-supplier of RAFI. The use of such by any third parties for their own purposes may infringe the rights of the respective entity holding those rights.

RAFI GmbH & Co. KG

Ravensburger Str. 128-134
88276 Berg / Ravensburg
Germany
www.rafi-group.com,
info.headquarters@rafi-group.com