

LogiLink®



Audio Converter

Analog to Digital SPDIF/COAX

Art. No.: CA0102

Convert stereo audio from R/L input to Coaxial and Toslink outputs simultaneously.

Features:

- » Supports uncompressed 2-channel LPCM digital audio signal output
- » Supports output sampling rate at 48 KHz
- » Provides electromagnetic-noise-free transmission
- » Easy to install and simple to operate

Specification:

Audio Input Connector	2 x RCA (R/L)
Audio Output Connector	Toslink, 1 x RCA (Coaxial)
Sampling Rate	48 KHz
Operating Temperature	0°C to +70°C
Operating Humidity	10% to 85 % RH (no condensation)
Storage Temperature	-10°C to +80°C
Storage Humidity	5% to 90 % RH (no condensation)
Power Supply	DC 5V/1A
Power Consumption	0.5 Watts (max)
Product Dimension	64(L) x 41(W) x 26(H)mm
Product Weight	78g



RoHS
compliant



* The specifications and pictures are subject to change without notice.
* All trade names referenced are the registered trademark of their respective owners.



CA0102



4 052792 044812

Made in China

LogiLink®



Audio Converter

Analog to Digital SPDIF/COAX

Art. No.: CA0102



Package Contents:

- » 1 x Audio Converter
- » 1 x Power Supply
- » 1 x User Manual

Package Informations:

- » Packing Dimension: 149 x 110 x 40mm
- » Packing Weight: 0.13kg
- » Carton Dimension: 575 x 235 x 340mm
- » Carton Q'ty: 50pcs
- » Carton Weight: 9.8kg

Best Connectivity



RoHS
compliant



* The specifications and pictures are subject to change without notice.
* All trade names referenced are the registered namework of their respective owners.



4 052792 044812

Made in China