





Art No. HS0002

Stereo HeadsetWith Volume Control and Microphone

Feature:

- Stereo-Headset with head frame
- · Light weight
- Volume controller integrated into the cable
- For internet-telephony and web programs
- · Colored audio plugs making it easier to plug the cables into your audio card

Specification:

- Microphone type: 9mm x 7mm
- Impedance: maximum 2.2K
- Sensitivity: -58db+/-2dB (Odb-1vv/pa)
- Directivity: Omni-directional
- S/N ratio: more than 60dB
- Sensitivity reduction: within-3dB at 1.5V
- Microphone frequency: 30Hz-16000Hz
- Speaker: 30mm
- Sensitivity: 98dB SP.L at 1KHz
- Speaker frequency: 20Hz-20000Hz
- Impedance: 32ohms
- Cold length: about 1.8m
- Connection: 3.5 stereo plugs x 2
- With volume control and microphone
- Color: Black

Packaging Information:

- Packing Dimension: 171x248x53 mm
- Packing Weight: 0.11kg
- Carton Dimension: 540x260x340 mm
- Carton Q'ty: 40pcs
- Carton Weight: 6kgs





