

LogiLink®

Illuminated Keyboard

Art. No.: ID0138



Experience the typing comfort with magnificent rainbow lighting!

Features:

- » Rainbow LED backlighting
- » Keyboard with 104 keys in German layout
- » Num lock/Caps lock/Scroll lock LED indicators
- » USB interface
- » Compatible with Windows, Mac OS and Android



Specification:

Interface	USB 1.1
Keyboard Type	Membrane structure
Keycap Quantity	Standard keyboard 104 keys
Keycap Style	High keycap
Actuation Force	F1(FP): 50g±8g
Full Travel	4.0mm±0.5mm
Backlight	Rainbow LED backlight (Press Scroll key to turn on/off)
Actuation Force	50gf±10gf
Full Travel	4.0mm±0.4mm
Life Span (Keystrokes)	Around 5 million cycles (normal operating force)
USB Power Source	5V/0.12A (LED backlight ON), 0.04A (LED backlight OFF)
Dimension (L x W x H)	438 x 127 x 28mm
Weight	513g±10g (cable included)
Cable Length	160cm±5cm (4pin USB cable)

System Requirements:

- » Available USB port
- » Windows XP / ME / Vista / 7 / 8 / 10 / Android / Mac OS 10 or higher



ID0138



4 052792 041668

Made in China



RoHS
compliant



* The specifications and pictures are subject to change without notice.
* All trade names referenced are the registered trademark of their respective owners.

LogiLink®

Illuminated Keyboard

Art. No.: ID0138



Package Contents:

- » 1x Illuminated Keyboard
- » 1x User Manual

Package Informations:

- » Packing Dimension: mm
- » Packing Weight: kg
- » Carton Dimension: mm
- » Carton Q'ty: pcs
- » Carton Weight: kg



Best Connectivity



RoHS
compliant



* The specifications and pictures are subject to change without notice.
* All trade names referenced are the registered trademark of their respective owners.



ID0138



4 052792 041668

Made in China