

Fiber Patch Cord OS2 9/125 μ

Technical Features

Duplex Patch Cable 9/125 μ single mode, complies to G652.D standard

I-VH 2G 9/125 μ OS1/2 fiber, high-quality and better compatibility with barebone or indoor-coming components

Ø2mm orange double-layer LSZH Jacket according to IEC standard, meeting all European countries' legal requirement

First-class CCTC Class A Ferrule

Up to 100 Gbit/s/40km

All components in aspect of material and measurement are compliant with IEC standard

DIN EN 50173-1 and IEC/ISO 11801

Pulling force of Connector is compliant with IEC standard

Test method of Insertion Loss and return Loss is compliant with IEC standard

Test method of surface hygiene is compliant with IEC Standard

100% IL and RL Test for patch cords and pigtails

100% IL for each port of Adapter

100% End face Control

20% 3D Random Test to guarantee 90% the 3D Pass Quote

Cable length with positive tolerance

Each cable includes a measure protocol

Quality Management according to ISO 90001

Connector polishing: Ultra physical contact (UPC)


www.logilink.com




RoHS
compliant



Technical Drawings



Length	LC-LC	EAN Code
0.50 m	FP0LC00	4052792019261
1.00 m	FP0LC01	4052792019278
2.00 m	FP0LC02	4052792019285
3.00 m	FP0LC03	4052792019292
5.00 m	FP0LC05	4052792019308
7.50 m	FP0LC07	4052792019315
10.00 m	FP0LC10	4052792019322
15.00 m	FP0LC15	4052792019339
20.00 m	FP0LC20	4052792019346



Length	SC-SC	EAN Code	Length	LC-SC	EAN Code
0.50 m	FPOSC00	4052792019353	0.50 m	FP0LS00	4052792019537
1.00 m	FPOSC01	4052792019360	1.00 m	FP0LS01	4052792019544
2.00 m	FPOSC02	4052792019377	2.00 m	FP0LS02	4052792019551
3.00 m	FPOSC03	4052792019384	3.00 m	FP0LS03	4052792019568
5.00 m	FPOSC05	4052792019391	5.00 m	FP0LS05	4052792019575
7.50 m	FPOSC07	4052792019407	7.50 m	FP0LS07	4052792019582
10.00 m	FPOSC10	4052792019414	10.00 m	FP0LS10	4052792019599
15.00 m	FPOSC15	4052792019421	15.00 m	FP0LS15	4052792019605
20.00 m	FPOSC20	4052792019438	20.00 m	FP0LS20	4052792019612

Length	LC-ST	EAN Code	ST-SC	EAN Code
0.50 m	FPOLT00	4052792019629	FPOSS00	4052792019711
1.00 m	FPOLT01	4052792019636	FPOSS01	4052792019728
2.00 m	FPOLT02	4052792019643	FPOSS02	4052792019735
3.00 m	FPOLT03	4052792019650	FPOSS03	4052792019742
5.00 m	FPOLT05	4052792019667	FPOSS05	4052792019759
7.50 m	FPOLT07	4052792019674	FPOSS07	4052792019766
10.00 m	FPOLT10	4052792019681	FPOSS10	4052792019773
15.00 m	FPOLT15	4052792019698	FPOSS15	4052792019780
20.00 m	FPOLT20	4052792019704	FPOSS20	4052792019797

Package Content

1 x Fiber Patch Cord OS2 9/125 μ

Packaging Information

Packing Dimension	180 x 180mm (0.50m - 2.0m items) / 220 x 220mm (3.00m - 20.00m items)
Packing Weight	0.01kg (0.50m items) / 0.02kg (1.00m items) / 0.04kg (2.00m items) / 0.06kg (3.00m items) / 0.09kg (5.00m items) / 0.14kg (7.50m items) / 0.17kg (10.00m items) / 0.26kg (15.00m items) / 0.37kg (20.00m items)
Carton Dimension	217 x 217 x 220mm
Carton Q'ty	pcs
Carton Weight	0.96kg (0.50m items) / 1.38kg (1.00m items) / 1.60kg (2.00m items) / 2.25kg (3.00m & 5.00m items) / 2.63kg (10.00m - 20.00m items) / 2.83kg (7.50m items)

