

Gigabyte GT 1030 Low Profile D4 2G - Grafikkarten - GF GT 1030 - 2 GB

Produktbeschreibung:	Gigabyte GT 1030 Low Profile D4 2G - Grafikkarten - GF GT 1030 - 2 GB DDR4 - PCIe 3.0 Low-Profile - DVI, HDMI
Gruppe:	Videokarten
Hersteller:	GIGABYTE
Hersteller Artikel Nr:	GV-N1030D4-2GL
EAN:	4719331303280



Hauptmerkmale

Produktbeschreibung	Gigabyte GT 1030 Low Profile D4 2G - Grafikkarten - GF GT 1030 - 2 GB
Gerätetyp	Grafikkarten - Low-Profile
Bustyp	PCI Express 3.0
Grafik-Engine	NVIDIA GeForce GT 1030
Speicher	2 GB DDR4
Core Clock	1177 MHz
Boost-Takt	1417 MHz
CUDA-Kerne	384
Effektiver Speichertakt	2100 MHz
Speicherschnittstelle	64-Bit
Max Auflösung	4096 x 2160
Anzahl der max. unterstützten Bildschirme	2
Schnittstellen	DVI-D HDMI
API-Unterstützung	DirectX 12, OpenGL 4.5
Abmessungen (Breite x Tiefe x Höhe)	1.47 cm x 14.99 cm x 6.89 cm

What's in the Box:

- Gigabyte GT 1030 Low Profile D4 2G
- Low profile Slotblech

