

Kingston FURY Renegade - DDR4 - Kit - 32 GB: 2 x 16 GB - DIMM 288-PIN - 4266 MHz / PC4-34100 - ungepuffert

Produktbeschreibung: Kingston FURY Renegade - DDR4 - Kit - 32 GB: 2 x 16 GB - DIMM 288-PIN - 4266 MHz / PC4-34100 - CL19 - 1.4 V - ungepuffert - non-ECC - Schwarz

Gruppe: RAM
 Hersteller: Kingston
 Hersteller Artikel Nr: KF442C19RB1K2/32
 EAN: 0740617322286



Hauptmerkmale

Produktbeschreibung	Kingston FURY Renegade - DDR4 - Kit - 32 GB: 2 x 16 GB - DIMM 288-PIN - 4266 MHz / PC4-34100 - ungepuffert
Produkttyp	Speicher-Kit
Kapazität	32 GB: 2 x 16 GB
Speichertyp	DDR4 SDRAM - DIMM 288-PIN
Erweiterungstyp	Generisch
Datenintegritätsprüfung	Non-ECC
Geschwindigkeit	4266 MHz (PC4-34100)
Latenzzeiten	CL19 (19-26-26)
Leistungsmerkmale	Dual Rank, On-Die Termination (ODT), Serial Presence Detect (SPD), Black PCB, sechzehn Bänke, Intel Extreme Memory Profiles (XMP 2.0), schwarzer Hitzeverteiler aus Aluminium, AMD Ryzen Ready, ungepuffert
Spannung	1.4 V
Metallüberzug	Gold

