

Kingston FURY Renegade - DDR4 - Modul - 8 GB - DIMM 288-PIN - 3000 MHz / PC4-24000 - ungepuffert

Produktbeschreibung: Kingston FURY Renegade - DDR4 - Modul - 8 GB - DIMM 288-PIN - 3000 MHz / PC4-24000 - CL15 - 1.35 V - ungepuffert - non-ECC - Schwarz

Gruppe: RAM
 Hersteller: Kingston
 Hersteller Artikel Nr: KF430C15RB/8
 EAN: 0740617322170

Hauptmerkmale

Produktbeschreibung	Kingston FURY Renegade - DDR4 - Modul - 8 GB - DIMM 288-PIN - 3000 MHz / PC4-24000 - ungepuffert
Produkttyp	Speichermodul
Kapazität	8 GB
Speichertyp	DDR4 SDRAM - DIMM 288-PIN
Erweiterungstyp	Generisch
Datenintegritätsprüfung	Non-ECC
Geschwindigkeit	3000 MHz (PC4-24000)
Latenzzeiten	CL15 (15-17-17)
Leistungsmerkmale	Single Rank, On-Die Termination (ODT), Serial Presence Detect (SPD), Black PCB, sechzehn Bänke, Intel Extreme Memory Profiles (XMP 2.0), schwarzer Hitzeverteiler aus Aluminium, AMD Ryzen Ready, ungepuffert
Spannung	1.35 V
Metallüberzug	Gold

