

DATA SHEET



edding 1800 profipen blue (0.1)

- Precision fineliner for writing and precise sketching on light-coloured paper
- The metal-framed plastic nib has a stroke width of approx. 0.25 mm
- The pigment ink is waterproof and extremely lightfast

Highlights

- Highly precise writing and sketching results
- Easy and clean to use for uncomplicated, spontaneous creativity
- Cap with practical metal clip - can be stored on end of barrel
- The cap has a high-quality stainless steel clip
- High-quality brand product

Art.No. **4-180001003**

GTIN **4004764043873**



DATA SHEET



Specifications

Model	e-1800
Shape of nib	Round nib
Stroke width	0,25 mm
Included colours	Blue
Number of available colours	4
Applicable on	Paper
Ink description	Water-based pigment ink
Lightfast	Yes
Waterproof	Yes
Refillable	No
Quick drying	Yes
Cap off	No
Material of barrel	Polypropylene (PP)
Material of nib / filter	Plastic / Polyester
Material of cap / mouthpiece	Polypropylene (PP) / -

Logistics

Quantity	1
Packing dimensions	13 x 135 x 13 (mm)
Weight (gross/net)	10.63 g / 9 g
Country of origin	Japan

DATA SHEET

Product overview

Article number	GTIN / EAN	Article name	Minimum order quantity
4-1800-3	4004764044603	edding 1800 profipen set of 3 black	1
4-180001-1-1001	4004764061686	edding 1800 profipen 0.1 blister of 1 black	10
4-180001001	4004764043859	edding 1800 0.1 profipen black	10
4-180001002	4004764043866	edding 1800 0.1 profipen red	10
4-180001003	4004764043873	edding 1800 0.1 profipen blue	10
4-180001004	4004764043880	edding 1800 0.1 profipen green	10
4-180003-1-1001	4004764061716	edding 1800 profipen 0.3 blister of 1 black	10
4-180003001	4004764044108	edding 1800 0.3 profipen black	10
4-180003002	4004764044115	edding 1800 0.3 profipen red	10
4-180003003	4004764044122	edding 1800 0.3 profipen blue	10
4-180003004	4004764044139	edding 1800 0.3 profipen green	10
4-180005-1-1001	4004764061747	edding 1800 profipen 0.5 blister of 1 black	10
4-180005001	4004764044351	edding 1800 0.5 profipen black	10
4-180005002	4004764044368	edding 1800 0.5 profipen red	10
4-180005003	4004764044375	edding 1800 0.5 profipen blue	10
4-180005004	4004764044382	edding 1800 0.5 profipen green	10
4-180007001	4004764325726	edding 1800 0.7 profipen black	10
4-180007002	4004764325733	edding 1800 0.7 profipen red	10
4-180007003	4004764325740	edding 1800 0.7 profipen blue	10
4-180007004	4004764325757	edding 1800 0.7 profipen green	10