


Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2013 with regard to energy labelling of electronic displays

	Parameter	Parameter or value and precision			Unit
1.	Supplier's name or trademark.	Alogic			
	Supplier's address.	Alogic Europe B.V., Kraijenhoffstraat 137A, 1018RG Amsterdam, NL			
2.	Model identifier	27C4KPDW			
3.	Energy Efficiency Class for Standard Dynamic Range (SDR)	F			
4.	On mode power demand in SDR	26,0			W
5.	Energy Efficiency Class for High Dynamic Range (HDR)	G			
6.	On mode power demand in HDR, if implemented	45,0			W
7.	Off mode, power demand, if applicable	0,2			W
8.	Standby mode power demand, if applicable	0,3			W
9.	Networked standby mode power demand, if applicable	n.a.			W
10.	Electronic display category	Monitor			
11.	Size ratio	16	:	9	
12.	Screen resolution	3 840	x	2 160	pixels
13.	Screen diagonal	68,5			cm
14.	Screen diagonal	27			inches
15.	Visible screen area	20,1			dm²
16.	Panel technology used	LED LCD			
17.	Automatic Brightness Control (ABC) available	No			
18.	Voice recognition sensor available	No			
19.	Room presence sensor available	No			
20.	Image refresh frequency rate (default)	60			Hz
21.	Minimum guaranteed availability of software and firmware updates (from the date of end of the placement on the market)	8			Years
22.	Minimum guaranteed availability of spare parts (from the date of end of the placement on the market)	7			Years
23.	Minimum guaranteed product support	7			Years
	Minimum duration of the general guarantee offered by the supplier	5			Years
24.	Power supply type	External			
25.	External power supply (non standardized and included in the product box)				
	i	(EU)2019/1782			
	ii	Input voltage	100		V

	<i>iii</i>	Output voltage	19,0	V
26.	External standardised power supply (or suitable one if not included in the product box)			
	<i>i</i>	-		
	<i>ii</i>	Required output voltage	-	V
	<i>iii</i>	Required delivered current (minimum)	-	A
	<i>iv</i>	Required current frequency	-	Hz

Model placed on the Union market from 01/10/2023



EPREL registration number: 1716043

<https://eprel.ec.europa.eu/qr/1716043>

Supplier: Alogic Europe B.V. (Importer)

Website:

Customer care service:

Name: Alogic Europe B.V.

Website:

Email: support@alogic.co

Phone: +61420509826

Address:

Kraijenhoffstraat 137A
1018RG Amsterdam
Netherlands