

VKSW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Wire channel cutter for manual operation in cutting wiring channels and covers up to 125 mm wide and a wall thickness of 2.5 mm. Only for plastics not reinforced by fillers.

- Cutting with no burrs or waste
- Length stop (1,000 mm) with guide device for precise cutting to length
- Table-top unit for mounting on a workbench or similar work surface
- Hardened cutting edges made of special steel

Általános rendelési adatok

Típus	VKSW
Rendelési szám	1137530000
Verzió	Cable duct cutting device
GTIN (EAN)	4032248919406
Menny.	1 Stück

VKSW

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Műszaki adatok

Méretek és tömegek

Szélesség	280 mm	Szélesség (coll)	11,024 inch
Magasság	285 mm	Magasság (coll)	11,22 inch
Mélység	290 mm	Mélység (coll)	11,417 inch
Tömeg	15 000 g	Nettó tömeg	10 700 g

Termék környezetvédelmi megfelelése

REACH SVHC Lead 7439-92-1

Besorolások

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000149
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	21-04-90-90	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	21-04-50-03
eClass 9.1	21-01-90-90		

Letöltések

Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)