

IE-KO-HAT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- Overpressure valve protects against overloading
- Cylinder head angled at 90°
- Angled head can be rotated through 360°
- Ergonomic handle springs back automatically
- The waste piece no longer becomes jammed thanks to triple splitting
- Hydraulic punch made of high-strength aluminium (approx. 40% weight saving)
- Service life greatly reduced when stainless steel sheets are used

Általános rendelési adatok

Típus	IE-KO-HAT
Rendelési szám	1966810000
Verzió	Lemezlyukasztó
GTIN (EAN)	4032248659630
Menny.	1 Stück

IE-KO-HAT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Műszaki adatok

Méretek és tömegek

Szélesség	290 mm	Szélesség (coll)	11,417 inch
Magasság	120 mm	Magasság (coll)	4,724 inch
Mélység	70 mm	Mélység (coll)	2,756 inch
Tömeg	1,9 kg	Nettó tömeg	3 262 g

Termék környezetvédelmi megfelelése

REACH SVHC Lead 7439-92-1

Vágószerszámok

Kerek furatok, Ø 1 - 85 mm	2,0 mm F = 370 N/mm ²	Kerek furatok, Ø 2 - 64 mm	3,0 mm F = 370 N/mm ²
Kerek furatok, Ø 3 - 64 mm	2,5 mm F = 600 N/mm ²	Lyukasztóerő	75 kN
Max. üzemi nyomás	650 bar	Négyszögletes furatok, max.	36 x 112 mm; 2,0 mm F = 370 N/mm ²
Négyszeges furatok, max.	68 x 68 mm; 2,0 mm F = 370 N/mm ²		

Besorolások

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000156
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-14-91-90	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	21-04-90-47
eClass 9.1	21-04-90-47		

Letöltések

Brochure/Catalogue [CAT 9 IETH 18/19 EN](#)
[CAT 3 HDC 17/18 EN](#)
[CAT 6 TOOLS 15/16 EN](#)
[CAT 5 ENCL 17/18 EN](#)

IE-KO-HAT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Rajzok

Felhasználási példa

