

WIL-MAGNET**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The WIL-STANDARD: 24V DC LED lamp, only 8mm high, with very high light output (1315 lm) and long service life (greater than 10,000 h).

Extremely robust construction, solid encapsulation and metal housing - waterproof (IP67).

Its 6500K colour temperature (daylight) makes it suitable for a wide range of applications.

Very easy to connect thanks to M12 connector. Low current consumption means that a 24V, 0.5A DC power supply is sufficient for operation.

Általános rendelési adatok

Típus	WIL-MAGNET
Rendelési szám	2526810000
GTIN (EAN)	4050118537871
Menny.	1 Stück

WIL-MAGNET

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Műszaki adatok

Méreték és tömegek

Nettó tömeg	10 g
-------------	------

Hőmérsékletek

Üzemi hőmérséklet, max.	60 °C	Üzemi hőmérséklet, min.	-20 °C
Üzemi hőmérséklet	-20 - 60°C		

Szabványok

Tanúsítvány száma (cULus)	E354496
---------------------------	---------

Besorolások

ETIM 6.0	EC002955	eClass 6.2	27-11-06-31
eClass 9.0	27-11-92-90	eClass 9.1	27-11-92-90

Jóváhagyások

Jóváhagyások



ROHS	Megfelel
------	----------

Letöltések

Engineering Data	STEP
Tervezési adatok	EPLAN

WIL-MAGNET

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Rajzok

