

EF 10 54 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats. Thought out details as the functional flap cover enable a fast and tool-less change of the filter mats which saves time and money.

Általános rendelési adatok

Típus	EF 10 54 GY
Rendelési szám	2557070000
Verzió	Exhaust filter, IP54, szürke
GTIN (EAN)	4050118567700
Menny.	1 Stück

EF 10 54 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Műszaki adatok

Méretek és tömegek

Szélesség	109 mm	Szélesség (coll)	4,291 inch
Magasság	109 mm	Magasság (coll)	4,291 inch
Mélység	23 mm	Mélység (coll)	0,906 inch
Nettó tömeg	60 g		

General data

Anyag	Hőre lágyuló műanyag	EMC változat	No
Felszerelés típusa	Felpattintható	Filter class	G 3
Height of installation cut-outs	92 mm	Mounting depth	19 mm
Mounting height	4 mm	Width of installation cut-outs	92 mm
With filter	Igen		

Besorolások

ETIM 6.0	EC002513	eClass 6.2	27-18-07-16
eClass 9.1	27-18-07-06		

Jóváhagyások

Jóváhagyások



ROHS

Megfelel

Letöltések

Engineering Data

[STEP](#)