

**REF 600 54 GY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats. Thought out details as the functional flap cover enable a fast and tool-less change of the filter mats which saves time and money.

**Általános rendelési adatok**

Típus	REF 600 54 GY
Rendelési szám	<a href="#">2557840000</a>
Verzió	Exhaust filter, IP54, szürke
GTIN (EAN)	4050118568486
Menny.	1 Stück

## REF 600 54 GY

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

## Műszaki adatok

## Méretek és tömegek

Szélesség	436 mm	Szélesség (coll)	17,165 inch
Magasság	436 mm	Magasság (coll)	17,165 inch
Mélység	252 mm	Mélység (coll)	9,921 inch
Nettó tömeg	2 500 g		

## General data

EMC változat	No	Felszerelés típusa	Felpattintható
Filter class	G 3	Height of installation cut-outs	291 mm
Mounting depth	34 mm	Mounting height	72 mm
Width of installation cut-outs	291 mm	With filter	Igen

## Besorolások

ETIM 6.0	EC002513	eClass 6.2	27-18-07-16
eClass 9.1	27-18-07-06		

## Jóváhagyások

Jóváhagyások



ROHS

Megfelel

## Letöltések

Engineering Data

[STEP](#)