

WIL-BM-SK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The WIL-STANDARD: 24V DC LED lamp, only 8mm high, with very high light output (1315 lm) and long service life (greater than 10,000 h).

Extremely robust construction, solid encapsulation and metal housing - waterproof (IP67).

Its 6500K colour temperature (daylight) makes it suitable for a wide range of applications.

Very easy to connect thanks to M12 connector. Low current consumption means that a 24V, 0.5A DC power supply is sufficient for operation.

Általános rendelési adatok

Típus	WIL-BM-SK
Rendelési szám	2537720000
GTIN (EAN)	4050118549157
Menny.	1 Stück

WIL-BM-SK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Műszaki adatok

Méretetek és tömegek

Nettó tömeg	35 g
-------------	------

Hőmérsékletek

Üzemi hőmérséklet, max.	60 °C	Üzemi hőmérséklet, min.	-20 °C
Üzemi hőmérséklet	-20 - 60°C		

Termék környezetvédelmi megfelelése

REACH SVHC	Lead 7439-92-1
------------	----------------

Connection data

Csatlakozási menet	Terminal	Vezetékezés	PIN 4: + (black), PIN 3: - (blue)
--------------------	----------	-------------	-----------------------------------

Electric data

Névleges feszültség (szöveg)	24 V DC
------------------------------	---------

Besorolások

ETIM 6.0	EC002955	eClass 6.2	27-11-06-31
----------	----------	------------	-------------

Jóváhagyások

Jóváhagyások



ROHS	Megfelel
------	----------

WIL-BM-SK

Rajzok

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

