

**Industrial Ethernet
IE-PIC-HYB-S-0,75-300****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Ibrido 10 poli Inserti per connettori Var.1 /4 /5 /14

Dati generali per l'ordinazione

Tipo	IE-PIC-HYB-S-0,75-300
Nr.Cat.	1068950000
Versione	Contatto a crimpare, Spina, Ibrido
GTIN (EAN)	4032248823109
CPZ	300 Pezzo

**Industrial Ethernet
IE-PIC-HYB-S-0,75-300**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Dati tecnici**Dimensioni e peso**

Peso netto 0,27 g

Conformità ambientale del prodotto

REACH SVHC Lead 7439-92-1

Dati generali

Sezione di collegamento cavo, flessibile, max.	0,75 mm ²	Sezione di collegamento cavo, flessibile, min.	0,75 mm ²
---	----------------------	---	----------------------

Proprietà elettriche

Tensione nominale 24 V

Classificazioni

ETIM 4.0	EC001264	ETIM 5.0	EC001264
ETIM 6.0	EC001121	eClass 6.2	27-25-05-04
eClass 7.1	27-25-05-04	eClass 8.1	19-17-01-25
eClass 9.0	27-44-03-90	eClass 9.1	27-44-09-90

Approvazioni

Omologazioni



ROHS Conforme

Downloads

Brochure/Catalogo	CAT 9 IETH 18/19 EN FL FIELDWIRING EN PI PROFINET CABLING EN
Documentazione utente	MAN IE GUIDE DE MAN IE GUIDE EN

**Industrial Ethernet
IE-PIC-HYB-S-0,75-300****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com**Disegni****Disegno quotato**