

**Industrial Ethernet
IE-BIC-HYB-P-0,5-300**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Ibrido 10 poli Inserti per connettori Var.1 /4 /5 /14

Dati generali per l'ordinazione

Tipo	IE-BIC-HYB-P-0,5-300
Nr.Cat.	1096150000
Versione	Contatto a crimpare, Flangia, Ibrido
GTIN (EAN)	4032248869114
CPZ	300 Pezzo

Industrial Ethernet IE-BIC-HYB-P-0,5-300

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Dati tecnici

Dimensioni e peso

Peso netto 0,29 g

Conformità ambientale del prodotto

REACH SVHC Lead 7439-92-1

Dati generali

Sezione di collegamento cavo, flessibile, max.	0,5 mm ²	Sezione di collegamento cavo, flessibile, min.	0,2 mm ²
---	---------------------	---	---------------------

Proprietà elettriche

Tensione nominale 24 V

Classificazioni

ETIM 3.0	EC000018	ETIM 4.0	EC000018
ETIM 5.0	EC000018	ETIM 6.0	EC001121
eClass 6.2	27-25-05-04	eClass 7.1	27-25-05-04
eClass 8.1	19-17-01-25	eClass 9.0	27-44-03-90
eClass 9.1	27-44-09-90		

Approvazioni

ROHS Conforme

Downloads

Brochure/Catalogo	CAT 9 IETH 18/19 EN FL FIELDWIRING EN PI PROFINET CABLING EN
Documentazione utente	MAN IE GUIDE DE MAN IE GUIDE EN

**Industrial Ethernet
IE-BIC-HYB-P-0,5-300**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Disegni**Disegno quotato**