

**IE-PP-V01P****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Per proteggere i vostri apparecchi da polvere e sporcizia.

**Dati generali per l'ordinazione**

Tipo	IE-PP-V01P
Nr.Cat.	<a href="#">1965690000</a>
Versione	Calotta protez. p. cust. connett.
GTIN (EAN)	4032248653911
CPZ	10 Pezzo

## IE-PP-V01P

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

## Dati tecnici

## Dimensioni e peso

Peso netto 11 g

## Temperature

Temperatura d'esercizio , max.	70 °C	Temperatura d'esercizio , min.	-40 °C
Temperatura d'esercizio	-40 °C...70 °C		

## Dati generali

Colori	Nero	Grado di protezione	IP67
Materiale base della custodia	PA 6 GF	Tipo di montaggio	Solo all'interno

## Classificazioni

ETIM 3.0	EC001121	ETIM 4.0	EC000437
ETIM 5.0	EC000437	ETIM 6.0	EC002040
UNSPSC	30-21-18-17	eClass 5.1	27-26-12-03
eClass 6.2	27-26-12-03	eClass 7.1	27-44-02-02
eClass 8.1	27-44-02-02	eClass 9.0	27-37-12-07
eClass 9.1	27-44-02-90		

## Approvazioni

Omologazioni



ROHS Conforme

## Downloads

Brochure/Catalogo	<a href="#">CAT 9 IETH 18/19 EN</a> <a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a>
Documentazione utente	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Omologazione/Certificato/Documento di conformità	<a href="#">UL Approval</a> <a href="#">GOST Approval</a>