



Squadretta di metallo, incluso pressacavo M20

Tipo SL7/4-FW-T
Catalog No. 171455
Alternate Catalog No. SL7/4-FW-T

Programma di fornitura

Assortimento			Accessori
Funzione base accessori			Squadretta di montaggio incluso pressacavo M20
Materiale			Acciaio inossidabile (angolo) Alluminio (Gewindeadapter)
Tipo di montaggio			Per montaggio verticale
			Guarnizione compresa nell'entità della fornitura
utilizzabile per			SL4-PIB-T... SL7-CB-T...
Collegamento a SmartWire-DT			no

Verifiche di progetto secondo IEC/EN 61439

Dati tecnici per verifiche di progetto			
Temperatura ambiente di servizio min.		°C	-30
Temperatura ambiente di servizio max.		°C	60

Dati tecnici secondo ETIM 7.0

apparecchi elettrici a bassa tensione (EG000017) / elemento di colonna segnaletica, angolare di fissaggio (EC001153)			
Tecnica Di Ar., Elettr., Energia, Tecn. Di Comm., Rete E Proc. Di Conduzione / Tecnologia Di Commutazione A Bassa Tensione / Unitó Di Comando E Segnalazione / Elemento colonna segnale, squadra di fissaggio (ecl@ss10.0.1-27-37-12-33 [AKF051014])			
tipo di montaggio			montaggio a parete
colore			altri

Approvazioni

Product Standards			IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
UL File No.			E29184
UL Category Control No.			NKCR
CSA File No.			UL report applies to both US and Canada
CSA Class No.			NKCR7
North America Certification			UL listed, certified by UL for use in Canada
Degree of Protection			UL Type 4, 4X, 13

Dimensioni

