

Contatto a crimpare - ST-06KS020 - 1607581

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Contatto a crimpare, tornito, Diametro contatto: 0,6 mm, Intervallo di crimpatura: 0,14 mm²...0,34 mm²

Key commercial data

package_quantity	100
GTIN	4046356272971

Technical data

Generalità

Esecuzione dei contatti	tornito
Diametro contatti	0,6 mm
Tipo contatti	femmina
Collegamento	Attacco a crimpare
Cicli di manovra meccanica	50
Sezione fili min.	0,14 mm ²
Sezione fili max.	0,34 mm ²

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260708
eCl@ss 7.0	27440312
eCl@ss 8.0	27440204

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000796
ETIM 5.0	EC000796

UNSPSC

UNSPSC 6.01	43172015
-------------	----------

Contatto a crimpare - ST-06KS020 - 1607581

classifications

UNSPSC

UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

approvals

GOST /

Approval details



accessories

SF-Z0054 - 1615585



Drawings

© Phoenix Contact 2014 - all rights reserved
<http://www.phoenixcontact.com>