

ANT 742P-DAB

Passive DAB/DAB+ antenna

CALIBER

Specifications

- Self adhesive (Glass Mount)
- 300cm wire length
- 90° angle Male SMA plug
- Freq.range: 174~237MHz / 470~958MHz
- DAB BIII / UHF 13~68CH
- Operating temp.: -40/+85 °C

- GB** **Passive DAB/DAB+ antenna**
300cm wire length,
90° angle Male SMA plug.
- F** **Passif DAB/DAB+ antenne**
300 cm de longueur de câble,
connecteur angle de 90° SMA mâle.
- D** **Passiv DAB/DAB+-Antenne**
300 cm Kabellänge,
90° Winkel männlich SMA-Stecker.
- I** **Passivo DAB/DAB+ antenna**
300 centimetri lunghezza del cavo,
90° angolo di connettore SMA maschio.
- E** **Pasivo DAB/DAB+ antena**
300 cm de longitud de cable,
conector SMA masculino 90° ángulo.
- P** **Passiva DAB/DAB+ antena**
300 centímetros comprimento do cabo,
90° conector SMA masculino ângulo.
- S** **Passiv DAB/DAB+ antenn**
300 cm kabel-längd,
90° vinkel manlig SMA-kontakt.
- PL** **Pasywny DAB/DAB+ antena**
długość kabla 300 cm,
90° kąt złącze męski SMA.
- GR** **Παθητικός DAB/DAB+ κεραία**
καλώδιο μήκους 300 εκατοστών,
90° αρσενικός βύσμα SMA γωνία.
- SK** **Pasívny DAB/DAB+ anténa**
- CZ** 300 cm délka kábla,
90° uhlová zásuvka SMA.
- NL** **Passieve DAB/DAB+ antenne**
300 cm kabellengte,
90° haakse mannelijke SMA stekker.



WWW.CALIBER.NL

CALIBER EUROPE BV · Kortakker 10 · 4264 AE Veen
The Netherlands