

**Industrial Ethernet
IE-CDM-V14MRJSCP/VAPM-C**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Delivery incl. dust caps

Media converter FreeCon Active PROFINET con funzionalità diagnostica, per connettore ad innesto PushPull Var. 14 a norma IEC 61076-3-117 con RJ45 e SC-RJ POF a norma IEC 61754-24 e PushPull Power ai sensi della specifica PROFINET.

Dati generali per l'ordinazione

Tipo	IE-CDM-V14MRJSCP/VAPM-C
Nr.Cat.	1324440000
Versione	Media converter POF, FreeCon
GTIN (EAN)	4050118128208
CPZ	1 Pezzo

Foglio dati

Industrial Ethernet IE-CDM-V14MRJSCP/VAPM-C

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Dati tecnici

Dimensioni e peso

Peso netto 722,04 g

Temperature

Temperatura d'esercizio , max.	55 °C	Temperatura d'esercizio , min.	-20 °C
Temperatura d'esercizio	-20 °C...55 °C	Temperatura di magazzino	
Temperatura di posa			

Conformità ambientale del prodotto

REACH SVHC Lead 7439-92-1

Norme

Connettori a norma	IEC 61076-3-117 var. 14, IEC 61754-24, IEC 60603-7-51	N° Certificato (cULus)	E141197
--------------------	---	----------------------------	---------

Proprietà elettriche

Baudrate	100 MB	Campo della tensione d'esercizio	18...30 V DC
Corrente assorbita		Indicatore a LED	P1: porta attiva, P2: porta attiva, SF: errore collettivo, BF: errore bus, US1: tensione 1 (elettronica), US2: tensione 2
Protocollo	tip. 200 mA PROFINET IRT	Tensione d'esercizio	24 V DC

Classificazioni

ETIM 6.0	EC001467	eClass 6.2	27-25-05-04
eClass 7.1	27-25-05-04	eClass 8.1	19-17-01-25
eClass 9.0	19-17-01-14	eClass 9.1	19-17-01-14

Approvazioni

Omologazioni



ROHS Conforme

**Industrial Ethernet
IE-CDM-V14MRJSCP/VAPM-C**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Dati tecnici**Downloads**

Brochure/Catalogo	CAT 9 IETH 15/16 EN FL FIELDWIRING EN PI PROFINET CABLING EN
Documentazione utente	Manual EN MAN IE GUIDE DE MAN IE GUIDE EN Firmware update manual Manual DE
Omologazione/Certificato/Documento di conformità	PI_Zertifikat_1324440000
Software	GSDML-V2.25-Weidmuller-FCAPIMPOF-20130124.zip WM_FCA_PIM_POF_V_1_04_01.zip CFG configurator - Weidmueller_FreeCon_08042011

**Industrial Ethernet
IE-CDM-V14MRJSCP/VAPM-C**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Disegni**Disegno quotato**